

**Part Number :** 2284101024
**Product Description :** Micro-Fit+ Female-to-Micro-Fit+ Female Off-the-Shelf (OTS) Cable Assembly, Dual Row, 500.00mm Length, Tin (Sn) Plating, 18 AWG, 2 Circuits, Black
**Series Number :** 228410
**Status :** Active
**Product Category :** Power and Signal Cable Assemblies

## Documents and Resources

### Drawings

2284101024_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Power and Signal Cable Assemblies |
| Series | 228410 |
| Description | Micro-Fit+ Female-to-Micro-Fit+ Female Off-the-Shelf (OTS) Cable Assembly, Dual Row, 500.00mm Length, Tin (Sn) Plating, 18 AWG, 2 Circuits, Black |
| Application | Wire-to-Board, Wire-to-Wire |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | Micro-Fit+-to-Micro-Fit+ |
| Product Name | Micro-Fit+ |
| Type | Discrete Wire Assembly |
| UPC | 198282852728 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 8.5A |
| Voltage - Maximum | 600V AC (RMS)/DC |

### Physical

| | |
|---|---|
| Cable Length | 500.00mm |
| Circuits (Loaded) | 2 |
| Circuits (maximum) | 2 |
| Color - Resin | Black |
| Gender | Female-Female |

Downloaded from Arrow.com.

| | |
|---|---|
| Lock to Mating Part | Yes |
| Material - Metal | High Conductivity Copper |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Nylon |
| Net Weight | 12.648/g |
| Number of Rows | 2 |
| Overmolded | No |
| Packaging Type | Bag |
| Pitch - Mating Interface | 3.00mm |
| Plating min - Mating | 2.500µm |
| Plating min - Termination | 2.500µm |
| Single Ended | No |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | Discrete Wire, UL 1061 |
| Wire Size (AWG) | 18 |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Micro-Fit+ Vertical, Dual Row, Through Hole Headers | 206832 |
| Micro-Fit+ Right-Angle, Dual Row, Through Hole Headers | 212528 |
| Micro-Fit+ Dual Row Surface Mount Headers | 218216 |
| Micro-Fit+ Versa Color Vertical, Dual Row, Through Hole Headers | 224246 |
| Micro-Fit+ Dual Row Plug Housings | 215922 |



Downloaded from Arrow.com.