
molex



Part Number : 751170118
Product Description : VHDM Single-Ended Board-to-Board Stacker Receptacle, 18mm Stack Height, 2.00mm Pitch, Vertical, 8 Rows, 80 Circuits, 0.76µm Gold (Au)
Series Number : 75117
Status : Obsolete
Product Category : Backplane Connectors

Obsolete

Documents and Resources

Drawings

751170118_sd.pdf

PK-70873-0750-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-74031-999-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Backplane Connectors
Series	75117
Description	VHDM Single-Ended Board-to-Board Stacker Receptacle, 18mm Stack Height, 2.00mm Pitch, Vertical, 8 Rows, 80 Circuits, 0.76µm Gold (Au)
Application	Board-to-Board Mezzanine
Comments	Stack Height 18.00mm, Lead-Free
Component Type	PCB Receptacle
Product Name	VHDM
UPC	756054905852

Agency

UL	E29179

Electrical

Current - Maximum per Contact	3.0A
Data Rate	3.125 Gbps
Voltage - Maximum	120V AC (RMS)/DC

Obsolete

Downloaded from Arrow.com.

Physical

Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	No
Keying to Mating Part	No
Material - Metal	Copper-Nickel-Silicon, High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	13.060/g
Number of Columns	10
Number of Pairs	Open Pin Field
Number of Rows	8
Orientation	Vertical
Packaging Type	Tube
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.80mm
PC Tail Length	2.85mm
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to PCB	No
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A

Obsolete

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
VHDM Single-Ended Backplane Headers	74060

Application Tooling

This document was generated on Jun 02, 2026

Obsolete

Downloaded from Arrow.com.