

4




3

2



1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DW	---	REVISED AS PER ECN-22-176158	28APR2022	I.T	S.Z



RECOMMENDED PCB LAYOUT (MOUNTING SIDE)
 THICKNESS 1.57mm (TOLERANCE: ±0.05)



NOTE:
 1. MATERIAL:
 HOUSING: PA9T WITH 33% GF, UL 94V-0, COLOR: SEE TABLE.
 CONTACTS: PHOSPHOR BRONZE.
 SHELL: SUS304, THICKNESS=0.40MM.
 MYLAR: POLYAMIDE FILM.
 2. FINISH:
 CONTACTS: GOLD FLASH OVER 0.762µm [30µ*] MIN. PALLADIUM-NICKEL OR ALTERNATIVE 0.762µm[30u"] MIN. GOLD PLATED ON CONTACT AREA,
 △ 2.54µm [100µ*] MIN. MATTE-TIN ON SOLDER TAIL,
 △ 2.54µm [100µ*] MIN. MATTE-TIN ON SOLDER TAIL,
 △ 3.05µm [120µ*] MIN. MATTE-TIN ON SOLDER TAIL,
 WITH ENTIRE CONTACT UNDERPLATED 1.27µm [50µ*] MIN. NICKEL.
 SHELL: △ & △ 1.27µm [50µ*] MIN. NICKEL PLATED OVERALL.
 △ 0.76µm [30µ*] MIN. MATTE-TIN OVER 1.27µm [50µ*] MIN. NICKEL.
 3. NO DATECODE ON PRODUCT SURFACE.
 4. REFLOW SOLDER CAPABLE TO 260°C PER TE TEST SPEC. 109-201, CONDITION B.

PLATED	HOUSING COLOR	MYLAR	LONG CARRIER & COVER TAPE	PACKAGE	POST	PART NUMBER
△	BLACK	W/O	W/O	TAPE REEL	W/	3-1734035-2
	BLACK	W/	W/O	TAPE REEL	W/	2-1734035-4
△	BLACK	W/O	W/	TAPE REEL	W/	2-1734035-3
	BLACK	W/O	N/A	TRAY	W/	2-1734035-2
	NATURAL	W/	W/O	TAPE REEL	W/	1734035-5
△	BLACK	W/	W/O	TAPE REEL	W/	1734035-4
	BLACK	W/O	W/	TAPE REEL	W/	1734035-3
	BLACK	W/O	W/O	TAPE REEL	W/	1734035-2
	BLACK	W/O	N/A	TRAY	W/	1734035-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HUI 21DEC2007				
DIMENSIONS: MM		CHK S. HOU 21DEC2007				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W. KODAMA 21DEC2007	NAME MINI USB, R/A, SMT, B TYPE			
0 PLC ± 0.38 1 PLC ± 0.25 2 PLC ± 0.13 3 PLC ± 0.05 4 PLC ± ANGLES ± 3°		PRODUCT SPEC 108-57062	QUALIFICATION TEST REPORT 501-57070	SIZE A3	CAGE CODE 00779	DRAWING NO C=1734035
MATERIAL SEE NOTE		FINISH SEE NOTE	WEIGHT --	RESTRICTED TO		
CUSTOMER DRAWING			SCALE --	SHEET 1 OF 4	REV G	

4




3

2




1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			



RECOMMENDED PCB LAYOUT (MOUNTING SIDE)
 THICKNESS 1.57mm (TOLERANCE:±0.05)



NOTE:

- MATERIAL:
 HOUSING: PA9T WITH 33% GF, UL 94V-0, BLACK COLOR.
 CONTACTS: PHOSPHOR BRONZE.
 SHELL: SUS304, THICKNESS=0.40MM.
 MYLAR: POLYAMIDE FILM.
- FINISH:
 CONTACTS: GOLD FLASH OVER 0.762µm [30µ*] MIN. PALLADIUM-NICKEL OR ALTERNATIVE 0.762µm[30u*] MIN. GOLD PLATED ON CONTACT AREA, 2.54µm [100µ*] MIN. MATTE-TIN ON SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED 1.27µm [50µ*] MIN. NICKEL.
 SHELL: 1.27µm [50µ*] MIN. NICKEL PLATED OVERALL.
- NO DATECODE ON PRODUCT SURFACE.
- REFLOW SOLDER CAPABLE TO 260°C PER TE TEST SPEC. 109-201, CONDITION B.

W/	W/O	TAPE REEL	W/O	4-1734035-2
	W/	TAPE REEL	W/O	1-1734035-3
W/O	W/O	TAPE REEL	W/O	1-1734035-2
	N/A	TRAY	W/O	1-1734035-1
MYLAR	LONG CARRIER & COVER TAPE	PACKAGE	POST	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN				
DIMENSIONS: MM		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME			
0 PLC ± 0.38 1 PLC ± 0.25 2 PLC ± 0.13 3 PLC ± 0.05 4 PLC ± ANGLES ± 3°		PRODUCT SPEC	MINI USB, R/A, SMT, B TYPE			
MATERIAL		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE NOTE		WEIGHT	A3	00779	C=1734035	
FINISH		CUSTOMER DRAWING	SCALE	SHEET	2 of 4	REV G
SEE NOTE						

4



3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			








8.25 Kg	5.55 Kg	150	56	8400 PCS	2-1734035-1
					1-1734035-1
					1734035-1
GROSS WEIGHT	NET WEIGHT	PCS/TRAY	TRAYS /CARTON	QUANTITY	PART NUMBER

DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		TE Connectivity	
		0 PLC	± -	CHK		NAME	
		1 PLC	± -	APVD		MINI USB, R/A, SMT, B TYPE	
		2 PLC	± -	PRODUCT SPEC		SIZE	CAGE CODE
		3 PLC	± -	APPLICATION SPEC		A3	00779
		4 PLC	± -	WEIGHT		DRAWING NO	C=1734035
		ANGLES	± -			RESTRICTED TO	
MATERIAL	FINISH			CUSTOMER DRAWING		SCALE	SHEET
						-	3 OF 4
							REV G


4
 THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

2 1


LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DW	-	SEE SHEET 1.			



FOR 1734035-3, 1-1734035-3 AND 2-1734035-3 (LONG CARRIER & COVER TAPE)



FOR 1734035-2, 1734035-4, 1734035-5, 1-1734035-2, 3-1734035-2, 2-1734035-2, 2-1734035-4, 4-1734035-2



GROSS WEIGHT	NET WEIGHT	PCS/REER	REERS / CARTON	QUANTITY	MYLAR	LONG CARRIER & COVER TAPE	PART NUMBER
4.95 Kg	2.31 Kg	700	5	3500	W/	W/O	4-1734035-2
					W/O	W/O	3-1734035-2
					W/	W/O	2-1734035-4
					W/O	W/	2-1734035-3
					W/O	W/O	2-1734035-2
					W/O	W/	1-1734035-3
					W/O	W/O	1-1734035-2
					W/	W/O	1734035-5
					W/	W/O	1734035-4
					W/O	W/	1734035-3
					W/O	W/O	1734035-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN	CHK	APVD	NAME
0 PLC ± -	1 PLC ± -	PRODUCT SPEC	APVD	NAME	MINI USB, R/A, SMT, B TYPE
2 PLC ± -	3 PLC ± -	APPLICATION SPEC	APVD	NAME	MINI USB, R/A, SMT, B TYPE
4 PLC ± -	ANGLES ± -	WEIGHT	APVD	NAME	MINI USB, R/A, SMT, B TYPE
MATERIAL	FINISH	WEIGHT	APVD	NAME	MINI USB, R/A, SMT, B TYPE
		CUSTOMER DRAWING		SCALE	SHEET 4 OF 4

STE TE Connectivity

SIZE: A3 CAGE CODE: 00779 DRAWING NO: C=1734035 RESTRICTED TO: -