Ratings
Voltage: 150 V
Temperature: -40~70 °C

Conductor
Conductor count: 2
Gauge: 26 AWG 0.13 mm²
Material: Tinned copper strands
Strand size: ∅0.08 x 26
Resistance at 20 °C: 150 Ω /km max

Insulator
Material: HDPE
Color: white, black
Diameter: ∅0.9 ±0.10 mm
Nominal thickness: 0.20 mm
Resistance at 20 °C: 100 MΩ /km min


Wrap:
Material: cotton paper

Filler
Material: aramid fiber

Outer jacket
Material: TPU
Color: gray
Diameter: ∅3 ±0.20 mm
Nominal thickness: 0.50 mm

Tests
Tensility strength: 26 kgf min
Dielectric test: 1500 V dc for 1 minute without breakdown
Bend test at 200g, ±60°, 30 cycles/min: 15,000 cycle minimum





Revision:	Date:	Description:
A	08/23/2022	Initial release

Prepared: PB
Digitally signed by PB
Date: 2022.09.20 10:13:44 -07'00'

Verified: MP
Digitally signed by MP
Date: 2022.09.21 08:46:42 -07'00'

Dimensions are in millimeters.
Tolerances:
X: ± 0.5 mm
X.X: ± 0.3 mm
X.XX: ± 0.05 mm

Notes:
RoHS compliant
Jacket meets ISO 10993 Biological Compatibility
Phthalate and halogen free
Function test: no open, no short, no intermittent

Description:
Wire, 2C TS, 26 AWG, 150V, 70C, 3.0 mm, TPU, 75A, gray, WBL

TENSILITY
tel 1.541.323.3228 800 877.670.7118
fax 1.541.323.4202 web tensility.com

Size: A
Part number: 30-02706
Scale: 18:1
Sheet 1 of 1

To see a custom version of this cable assembly, call Tensility at 541-323-3228 or email engineering@tensility.com

5 4 3 2 1

Downloaded from Arrow.com.