



+ CONNECTORS
HOUSINGS



✓ Active

TE CONNECTIVITY (TE)
2X8POS MODU4 HOUSING
[AMPMODU](#) | [AMPMODU IV/V](#)

925370-8
TE Internal Number: 925370-8

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Centerline (mm) 2.54
Termination Method to Wire/Cable Crimp
Centerline (Pitch) (in) .1
Number of Rows 2
Row-to-Row Spacing 2.54 mm [.1 in]

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

AMPMODU IV GEHAEUSE, EINREIHIG Housing, Single Row
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
3D_IGS.ZIP
English

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

AMPMODU Mod 1/2 Wire To Board Standard Pressure Contact Interconnection System

PDF

English

Agency Approvals

Agency Approval Document

AMPMODU CONNECTOR REPORT (GERMANY)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Row-to-Row Spacing 2.54 mm [.1 in]
- Terminates To Printed Circuit Board
- Glow Wire Rating Standard Part - Not Glow Wire
- Strain Relief With
- Connector Type Housing
- Connector Style Receptacle
- Product Type Connector

Configuration Features

- Number of Rows 2
- Number of Positions 16

Electrical Characteristics

- Operating Voltage 250 VAC

Body Features

- Color Green

Contact Features

- Contact Type Socket

Termination Features

Termination Method to Wire/Cable Crimp

Mechanical Attachment

Mating Retention With

Mating Retention Type Lock

Mating Connector Lock Without

Mating Alignment Without

Mating Alignment Type Polarization

Housing Features

Centerline (mm) 2.54

Centerline (Pitch) (in) .1

Housing Material Polyamide 6.6 GF

Housing Color Green

Housing Configuration Both Ends Closed

Dimensions

Length (in) 4.99

Height (in) .21

Usage Conditions

Operating Temperature Range (°C) -65 – 105

Operation/Application

For Use With AMPMODU Mod II .025 inch Headers

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Quantity 25

Statement of Compliance

Statement of Compliance

PDF