



Part Number : [2283702115](#)

Product Description : Pre-Crimped Lead Micro-Fit+ PCIe CEM5 Signal Female-to-Pigtail, 1.00µm Tin (Sn) Plating, 450.00mm Length, 28 AWG, Black

Series Number : 228370

Status : Active

Product Category : Power and Signal Cable Assemblies




Documents and Resources

Drawings

[2283702115 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	228370
Description	Pre-Crimped Lead Micro-Fit+ PCIe CEM5 Signal Female-to-Pigtail, 1.00µm Tin (Sn) Plating, 450.00mm Length, 28 AWG, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-Fit+ PCIe Terminal-to-Pigtail
Keyword	Pre-Crimped Leads
Product Name	Micro-Fit+ PCIe
UPC	198282852667

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.805/g

Packaging Type	Bag
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	28

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-Fit+ PCIe CEM5 Dual Row Receptacle Housings	<u>219114</u>

This document was generated on Jan 28, 2026