

## 5A, 50V - 600V Super Fast Rectifier



### FEATURES

- AEC-Q101 qualified available
- High efficiency, low  $V_F$
- High current capability
- High surge current capability
- Low power loss
- UL Recognized File # E-326243
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
$I_F$	5	A
$V_{RRM}$	50 - 600	V
$I_{FSM}$	70	A
$T_J \text{ MAX}$	150	°C
Package	ITO-220AB	
Configuration	Dual dies	

### APPLICATIONS

- DC to DC converter
- Switching mode converters and inverters
- Freewheeling application


**ITO-220AB**


### ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	SFF 501G	SFF 502G	SFF 503G	SFF 504G	SFF 505G	SFF 506G	SFF 507G	SFF 508G	UNIT
Marking code on the device		SFF 501G	SFF 502G	SFF 503G	SFF 504G	SFF 505G	SFF 506G	SFF 507G	SFF 508G	
Repetitive peak reverse voltage	$V_{RRM}$	50	100	150	200	300	400	500	600	V
Reverse voltage, total rms value	$V_{R(\text{RMS})}$	35	70	105	140	210	280	350	420	V
Forward current	$I_F$	5								A
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	$I_{FSM}$	70								A
Junction temperature	$T_J$	-55 to +150								°C
Storage temperature	$T_{STG}$	-55 to +150								°C

**THERMAL PERFORMANCE**

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-case thermal resistance	$R_{\Theta JC}$	5.5	°C/W

**ELECTRICAL SPECIFICATIONS (T<sub>A</sub> = 25°C unless otherwise noted)**

PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode <sup>(1)</sup>	SFF501G	$V_F$	-	0.98	V
	SFF502G		-	1.30	V
	SFF503G		-	1.70	V
Forward voltage per diode <sup>(1)</sup>	SFF504G		-	0.98	V
	SFF505G		-	1.30	V
	SFF506G		-	1.70	V
Reverse current @ rated V <sub>R</sub> per diode <sup>(2)</sup>	T <sub>J</sub> = 25°C	$I_R$	-	10	μA
	T <sub>J</sub> = 100°C		-	400	μA
Junction capacitance per diode	SFF501G	$C_J$	70	-	pF
	SFF502G		50	-	pF
Junction capacitance per diode	SFF503G		70	-	pF
	SFF504G		50	-	pF
Reverse recovery time	SFF505G	$t_{rr}$	-	35	ns
	SFF506G		-	35	ns
Reverse recovery time	SFF507G		-	35	ns
	SFF508G		-	35	ns
Reverse recovery time		$I_F = 0.5A, I_R = 1.0A$ $I_{rr} = 0.25A$	$t_{rr}$	-	ns

**Notes:**

1. Pulse test with PW = 0.3ms
2. Pulse test with PW = 30ms

**ORDERING INFORMATION**

ORDERING CODE <sup>(1)(2)</sup>	PACKAGE	PACKING
SFF5xG	ITO-220AB	50 / Tube
SFF5xGH	ITO-220AB	50 / Tube


**Notes:**

1. "x" defines voltage from 50V(SFF501G) to 600V(SFF508G)
2. "H" means AEC-Q101 qualified


## CHARACTERISTICS CURVES

( $T_A = 25^\circ\text{C}$  unless otherwise noted)


**Fig.1 Forward Current Derating Curve**




**Fig.2 Typical Junction Capacitance**




**Fig.3 Typical Reverse Characteristics**



**Fig.4 Typical Forward Characteristics**




**Fig.5 Maximum Non-Repetitive Forward Surge Current**




## CHARACTERISTICS CURVES


( $T_A = 25^\circ\text{C}$  unless otherwise noted)

**Fig.6 Reverse Recovery Time Characteristic and Test Circuit Diagram**



NOTES: 1. Rise Time=7ns max. Input Impedance= 1 megohm 22pf  
2. Rise Time=10ns max. Source Impedance= 50 ohms



**PACKAGE OUTLINE DIMENSIONS**
**ITO-220AB**


DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	4.30	4.70	0.169	0.185
A2	2.30	2.96	0.091	0.117
b	0.50	0.90	0.020	0.035
b1	-	1.80	-	0.071
b2	0.95	1.45	0.037	0.057
c	0.46	0.76	0.018	0.030
c2	2.50	3.16	0.098	0.124
D	14.80	15.50	0.583	0.610
D1	2.40	3.20	0.094	0.126
D2	6.30	6.90	0.248	0.272
E	9.60	10.30	0.378	0.406
e	2.41	2.67	0.095	0.105
L	12.60	13.80	0.496	0.543
L4	-	4.10	-	0.161
P	3.00	3.40	0.118	0.134

**MARKING DIAGRAM**


P/N = Marking Code  
 G = Green Compound  
 YWW = Date Code  
 F = Factory Code

## **Notice**

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.