S1184-KIT-1 ✔ ACTIVE

RAYCHEM

TE Internal #: 369276-000

Syringe, 2 Packaging Quantity, 150 °C Temperature (Max), Epoxy Adhesives

View on TE.com >

Wire Protection & Management > Adhesives & Sealants > Epoxy Adhesives



Packaging Method: **Syringe**

Packaging Quantity: **2**

Heat Resistance Temperature (Max): **150 °C**

Features

Body Features

Color (Supplied)	Silver
Color (Cured)	Silver
Material Systems Code	10, 100, 25

Usage Conditions

Heat Resistance Temperature (Max)	150 °C

Packaging Features

Packaging Method	Syringe
Packaging Quantity	2

Other

Pot Life	60 minute
Curing Method	20 °C for 24 hr, 80 °C for 1 hr

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)


Downloaded from Arrow.com.

	Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # EK7325-000
234A042-25C-0




TE Part # EM1474-000
222S152-100C-0




TE Part # EK7348-000
222S152-100C-G28-0




TE Part # EK7355-000
222S163-25C-G28-0




TE Part # EK7356-000
222S174-25C-G28-0



TE Part # EK7347-000
222S142-100C-G28-0




TE Part # EK7305-000
222S132-100C-0




TE Part # EK7280-000
202S152-100C-0


Downloaded from Arrow.com.




TE Part # EK7313-000
222S163-100C-0




TE Part # EM0635-000
202S211-25C-0




TE Part # EM3621-000
214A011-25C-0




TE Part # EK7263-000
202K174-25C-02-0




TE Part # EK7290-000
202S174-25C-01-0




TE Part # EK7310-000
222S142-25C-0




TE Part # EK7276-000
202S142-100C-0




TE Part # EK7289-000
202S174-25C-0




TE Part # EK7301-000
222S121-25C-0



TE Part # EK7334-000
301A022-25C-0



TE Part # EK7287-000
202S163-25C-02-0



TE Part # EK7286-000
202S163-25C-0

Customers Also Bought



TE Part #4575670001
TMS-SCE-1K-3/4-2.0-9




TE Part #690921-000
W-040-04




TE Part #878462-000
S1125-KIT-1



TE Part #657863-000
S1125-KIT-8



TE Part #850863-000
TXR40AB90-1407BI



TE Part #1137553001
55A1121-26-0/9-9



TE Part #990207-000
TXR40AB00-1408BI

TE Part #RE11-442S
PLUG ASSY

Downloaded from Arrow.com.

TE Part #ZPF000000000109933
029-0037-22



TE Part #4-2319764-2
E STACK PIANO 4P G LONG T&R PD OFF

Documents

Datasheets & Catalog Pages

1654025_Sec5_Adhesives

English

Raychem Molded Parts Visual Guide

English

Solutions for Defense Applications Certified to VG Standards

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Downloaded from Arrow.com.