

preLink RJ45 HIFF module empty



Image is for illustration purposes only. Please refer to product description.

Part number	20 82 000 0002
Specification	preLink RJ45 HIFF module empty
HARTING eCatalogue	https://b2b.harting.com/20820000002

Identification

Category	Connectors
Series	preLink®
Element	Female module
Specification	without terminal block

Version

Termination method	preLink® IDC insulation displacement termination
Size	HIFF version

Technical characteristics

Limiting temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP20
Transmission characteristics	Cat. 6A Class E _A up to 500 MHz
Vibration resistance	5.72 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No



Pushing Performance

Material properties

REACH SVHC substances	No
-----------------------	----

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1863 DUXR2.E470046 CSA-C22.2 No. 182.4, No. 233-09 DUXR8.E470046
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	22 g
Country of origin	Latvia
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors