Part Number : 192110002
Product Description : Krimptite Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier
Series Number : 19211
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : WP-1210T
Packaging Alternative : 192110001 (Bag)



Documents and Resources

Drawings

192110002_sd.pdf

Specifications

PS-19902-011-001.pdf

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	19211
Description	Krimptite Wire Pin Terminal for 12-10 AWG Wire, Mylar Tape Carrier
Application	Wire-to-Component
Comments	Pin Length 10.90mm
Product Name	Wire Pin,Krimptite
UPC	800753053205

Agency

CSA	LR18689
UL	E32244

Physical

Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.465/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.45mm max.
Wire Size (AWG)	10, 12
Wire Size mm^2	N/A

Downloaded from Arrow.com.

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270088
Mini-Mac Applicator	638851000

Downloaded from Arrow.com.