

Features

Regulated Converters

- Universal Input 85-305VAC
- Regulated Power Supply
- Continuous Short Circuit Protection
- Isolated Output 3kVAC / 1 min
- Meet EN55022 and FCC Class B
- Ultra-low Stand-By Power Consumption

Selection Guide

Part Number	Input Voltage (VAC)	Output Voltage (VDC)	Output Current (mA)	Typical Efficiency (%)	Max. Capacitive Load ⁽¹⁺²⁾
RAC03-3.3SCR/277*	85-305	3.3	900	68	22000µF
RAC03-05SCR/277*	85-305	5	600	70	10000µF
RAC03-12SCR/277*	85-305	12	250	74	1500µF
RAC03-24SCR/277*	85-305	24	125	76	200µF

* add „-Tray“ for Tray packaging, e.g. RAC03-05SCR/277-Tray

Specifications (measured at TA 25°C, full load after warm-up)

Input Voltage Range	85-305VAC or 120-430VDC	
Rated Power	3 Watts	
Input Frequency Range (for AC Input)	47-440Hz	
Input Current (Full Load)	115VAC / 230VAC	70mA / 45mA typ.
No Load Power Consumption	85-305VAC / 47-440Hz	75mW max.
Inrush Current (<2ms)	115VAC	15A max.
	230VAC	30A max.
Output Voltage	3.3V-24V	
Output Voltage Tolerance ⁽³⁾	3.3V	±4% typ. / ±8% max.
	5V	±3.5% typ. / ±5% max.
	12V / 24V	±3% typ. / ±4% max.
Output Current	see Selection Guide	
Output Ripple & Noise ⁽⁴⁾	3.3V	250mVp-p
	5V	200mVp-p
	12V / 24V	150mVp-p
Switching Frequency	@ Full Load	45KHz typ.
Hold-up Time	115VAC	18ms min.
Minimum Load	10%	
Line Voltage Regulation	LL-HL @ Full Load	±0.7% typ. / ±1% max.
Load Regulation (10%-100% Load)	3.3V	±5.5% typ. / ±9% max.
	5V	±5% typ. / ±7.5% max.
	12V, 24V	±4% typ. / ±5.5% max.
Leakage Current	85-305VAC / 47-440Hz	10uA max.
Isolation Voltage	3kVAC / 1minute	
Isolation Resistance	1GΩ min	
Short Circuit Protection	Continuous, Auto Restart	
Over Current Limit	105% - 150%	
Over Voltage Protection (Zener diode clamp)	130%-160%	
Over Voltage Category	OVC II	
Operating Temperature Range ⁽⁵⁾	natural convection, without derating	-25°C to +75°C
	natural air convection, with derating	-25°C to +85°C
Storage Temperature Range	-40°C to +85°C	
Relative Humidity	95% RH max.	
Case Material	UL94V-0 Black Plastic	
Potting Material	Epoxy	

continued on next page

POWERLINE

AC/DC-Converter

with 3 year Warranty

RECOM


3 Watt Single Output



CE Marked
UL-60950-1 Certified

RAC03-SCR/277

Derating-Graph (Ambient Temperature)



Refer to Application Notes

Specifications (measured at TA 25°C, full load after warm-up)

Package Weight	41g typ.		
Package Quantity	12pcs		
	„-Tray“-Version	72pcs	
Physical Dimension (LxWxH)	50.3 x 50.3 x 11.0mm		
RoHS	Test Report: KA/2012/91224		
EMC	EN55022 Class B		
Certifications			
UL General Safety	File Number: E224736	UL-60950-1	
EN General Safety	Report: TI20925N01-E	EN-55022: 2010 Class B, EN-55024:2010	
MTBF	TA = 25°C	1300 x 10 ³ hours	
(using MIL-HDBK-217F)	TA = 75°C	160 x 10 ³ hours	

Notes:

Note1: Measured @ 230VAC / 50Hz / Ta=25°C with constant resistant mode at full load.

Note2: If used @ 115VAC / 60Hz with full load, max. capacitive load is less, please contact RECOM for detailed information.


Note3: The “output voltage tolerance” includes initial voltage accuracy, thermal drift, line regulation and load regulation at rated input voltage and load conditions.

Note4: “Ripple and Noise” is the maximum peak-to-peak voltage value measured at the output with a 20 MHz bandwidth, at rated line voltage at full load.


Note5: Start up only is guaranteed at temperatures down to -25°C. Other specifications may not be met.

Typical Characteristics



Ambient Temperature vs. Input Voltage



Efficiency vs. Load



Mechanical Dimension



Wire Connections

Wire #			
1 (Brown)	AWG#22	1015	VAC in (L)
2 (Blue)	AWG#22	1015	VAC in (N)
3 (Red)	AWG#22	1430	+VDC out
4 (Black)	AWG#22	1430	-VDC out

Tolerance ±0.5mm unless otherwise specified

The product information and specifications are subject to change without prior notice. RECOM products are not authorized for use in safety-critical applications (such as life support) without RECOM's explicit written consent. A safety-critical application is defined as an application where a failure of a RECOM product may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The buyer shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.