

NTNS3A91PZ

MOSFET – Single, P-Channel, Small Signal, XLLGA3, 0.62 x 0.62 x 0.4 mm -20 V, -223 mA

Features

- Single P-Channel MOSFET
- Ultra Small and Thin Package (0.62 x 0.62 x 0.4 mm)
- Low $R_{DS(on)}$ Solution in 0.62 x 0.62 mm Package
- 1.5 V Gate Voltage Rating
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- Small Signal Load Switch
- Analog Switch
- High Speed Interfacing
- Optimized for Power Management in Ultra Portable Products

MAXIMUM RATINGS ($T_J = 25^\circ\text{C}$ unless otherwise stated)

| Parameter | Symbol | Value | Units |
|---|------------------------|--------------------------|-------|
| Drain-to-Source Voltage | V_{DSS} | -20 | V |
| Gate-to-Source Voltage | V_{GS} | ± 8.0 | V |
| Continuous Drain Current (Note 1) | I_D | -223 | mA |
| | | -161 | |
| | | -240 | |
| Power Dissipation (Note 1) | Steady State | $T_A = 25^\circ\text{C}$ | mW |
| | | $T_A = 85^\circ\text{C}$ | |
| Pulsed Drain Current | $t_p = 10 \mu\text{s}$ | P_D | mW |
| | | 121 | |
| | | 140 | |
| Pulsed Drain Current | I_{DM} | -669 | mA |
| Operating Junction and Storage Temperature | T_J, T_{STG} | -55 to 150 | °C |
| Source Current (Body Diode) | I_S | -121 | mA |
| Lead Temperature for Soldering Purposes (1/8" from case for 10 s) | T_L | 260 | °C |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

THERMAL RESISTANCE RATINGS

| Parameter | Symbol | Max | Units |
|---|-----------------|------|-------|
| Junction-to-Ambient – Steady State (Note 1) | $R_{\theta JA}$ | 1035 | °C/W |
| Junction-to-Ambient – $t \leq 5 \text{ s}$ (Note 1) | $R_{\theta JA}$ | 895 | |

1. Surface Mounted on FR4 Board using the minimum recommended pad size, (or 2 mm²), 1 oz Cu.




ON Semiconductor®

<http://onsemi.com>

MOSFET

| $V_{(\text{BR})DSS}$ | $R_{DS(\text{on}) \text{ MAX}}$ | $I_D \text{ MAX}$ |
|----------------------|---------------------------------|-------------------|
| -20 V | 1.6 Ω @ -4.5 V | -223 mA |
| | 2.4 Ω @ -2.5 V | |
| | 3.3 Ω @ -1.8 V | |
| | 4.5 Ω @ -1.5 V | |

P-Channel MOSFET



MARKING DIAGRAM



D = Specific Device Code
M = Date Code

ORDERING INFORMATION

| Device | Package | Shipping [†] |
|---------------|------------------|-----------------------|
| NTNS3A91PZT5G | XLLGA3 (Pb-Free) | 8000 / Tape & Reel |

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

NTNS3A91PZ

2. Pulse Test: pulse width $\leq 300 \mu\text{s}$, duty cycle $\leq 2\%$.

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified)

| Parameter | Symbol | Test Condition | Min | Typ | Max | Units |
|---|---------------------------------|---|------|------|-----------|----------------------------|
| OFF CHARACTERISTICS | | | | | | |
| Drain-to-Source Breakdown Voltage | $V_{(\text{BR})\text{DSS}}$ | $V_{\text{GS}} = 0 \text{ V}$, $I_D = -250 \mu\text{A}$ | -20 | | | V |
| Drain-to-Source Breakdown Voltage Temperature Coefficient | $V_{(\text{BR})\text{DSS}/T_J}$ | $I_D = -250 \mu\text{A}$, ref to 25°C | | 11 | | $\text{mV}/^\circ\text{C}$ |
| Zero Gate Voltage Drain Current | I_{DSS} | $V_{\text{GS}} = 0 \text{ V}$, $V_{\text{DS}} = -20 \text{ V}$ | | | -1.0 | μA |
| Gate-to-Source Leakage Current | I_{GSS} | $V_{\text{DS}} = 0 \text{ V}$, $V_{\text{GS}} = \pm 8.0 \text{ V}$ | | | ± 2.0 | μA |
| ON CHARACTERISTICS (Note 3) | | | | | | |
| Gate Threshold Voltage | $V_{\text{GS}(\text{TH})}$ | $V_{\text{GS}} = V_{\text{DS}}$, $I_D = -250 \mu\text{A}$ | -0.4 | | -1.0 | V |
| Negative Threshold Temperature Coefficient | $V_{\text{GS}(\text{TH})/T_J}$ | | | 2.1 | | $\text{mV}/^\circ\text{C}$ |
| Drain-to-Source On Resistance | $R_{\text{DS}(\text{on})}$ | $V_{\text{GS}} = -4.5 \text{ V}$, $I_D = -100 \text{ mA}$ | | 1.1 | 1.6 | Ω |
| | | $V_{\text{GS}} = -2.5 \text{ V}$, $I_D = -50 \text{ mA}$ | | 1.5 | 2.4 | |
| | | $V_{\text{GS}} = -1.8 \text{ V}$, $I_D = -20 \text{ mA}$ | | 2.0 | 3.3 | |
| | | $V_{\text{GS}} = -1.5 \text{ V}$, $I_D = -10 \text{ mA}$ | | 2.5 | 4.5 | |
| Forward Transconductance | g_{FS} | $V_{\text{DS}} = -5 \text{ V}$, $I_D = -100 \text{ mA}$ | | 0.41 | | S |
| Source-Drain Diode Voltage | V_{SD} | $V_{\text{GS}} = 0 \text{ V}$, $I_S = -10 \text{ mA}$ | | -0.6 | -1.0 | V |

CHARGES & CAPACITANCES

| | | | | | | |
|------------------------------|----------------------------|---|--|------|--|----|
| Input Capacitance | C_{ISS} | $V_{\text{GS}} = 0 \text{ V}$, $f = 10 \text{ kHz}$, $V_{\text{DS}} = -15 \text{ V}$ | | 41 | | pF |
| Output Capacitance | C_{OSS} | | | 4.6 | | |
| Reverse Transfer Capacitance | C_{RSS} | | | 4.1 | | |
| Total Gate Charge | $Q_{\text{G}(\text{TOT})}$ | $V_{\text{GS}} = -4.5 \text{ V}$, $V_{\text{DS}} = -15 \text{ V}$, $I_D = -200 \text{ mA}$ | | 1.1 | | nC |
| Threshold Gate Charge | $Q_{\text{G}(\text{TH})}$ | | | 0.1 | | |
| Gate-to-Source Charge | Q_{GS} | | | 0.2 | | |
| Gate-to-Drain Charge | Q_{GD} | | | 0.23 | | |

SWITCHING CHARACTERISTICS, $V_{\text{GS}} = 4.5 \text{ V}$ (Note 3)

| | | | | | | |
|---------------------|----------------------------|--|--|-----|--|----|
| Turn-On Delay Time | $t_{\text{d}(\text{ON})}$ | $V_{\text{GS}} = -4.5 \text{ V}$, $V_{\text{DD}} = -15 \text{ V}$, $I_D = -200 \text{ mA}$, $R_G = 2 \Omega$ | | 41 | | ns |
| Rise Time | t_r | | | 97 | | |
| Turn-Off Delay Time | $t_{\text{d}(\text{OFF})}$ | | | 571 | | |
| Fall Time | t_f | | | 286 | | |

3. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate-to-Source Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On Resistance Variation with Temperature










Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS





Figure 13. FET Thermal Response



*Dependent upon end user capabilities, this footprint could be used as a minimum.




SCALE 8:1

XLLGA3, 0.62x0.62, 0.35P

CASE 713AB

ISSUE O

DATE 25 SEP 2012



NOTES:


1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.

| DIM | MILLIMETERS | |
|-----|-------------|-------|
| | MIN | MAX |
| A | 0.340 | 0.440 |
| A1 | 0.000 | 0.030 |
| b | 0.100 | 0.200 |
| D | 0.620 BSC | |
| D2 | 0.175 BSC | |
| D3 | 0.205 BSC | |
| E | 0.620 BSC | |
| E2 | 0.400 | 0.600 |
| e | 0.350 BSC | |
| K | 0.200 REF. | |
| L | 0.090 | 0.210 |
| L2 | 0.110 | 0.310 |

GENERIC
MARKING DIAGRAM*

X = Specific Device Code
M = Date Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G", may or not be present.



DIMENSIONS: MILLIMETERS

*For additional information on our Pb-Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, [SOLDERRM/D](#).

| | | |
|------------------|--------------------------|---|
| DOCUMENT NUMBER: | 98AON84074E | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION: | XLLGA3, 0.62X0.62, 0.35P | PAGE 1 OF 1 |

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

