




RECOMMENDED PCB LAYOUT

Technical data

- 1.Nominal voltage: 300V/15A
PITCH:7.62mm
- 2.Insulation Withstanding Voltage:
AC 1600V/MIN
- 3.Insulation Resistance:
1000MΩ or more at DC500V
- 4.Operating temperature range:-40°C~115°C
- 5.Soldering temperature range:250°C±10°C/5sec
- 6.Safety approval:
- 7.RoHS Compliance
- 8.Undimensioned Tolerances:

Dim.L=Px7.62 Dim.B=(P-1)x7.62 P= number of poles 2-16P		
0-30mm	±0.15	±0.20
over 30mm-60mm	±0.20	±0.25
over 60mm-90mm	±0.25	±0.30
over 90mm	±0.30	±0.40

Part No.:

OSTOQXX0151

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	2: Red
...	3: Orange
16 16 Poles	4: Yellow
	5: Green (Standard)
	6: Blue
	8: Grey
Nonstandard colors Mins could apply	

2	PIN	COPPER	TIN PLATED	P
1	BODY	PA66 UL94V-0	ALL COLOR	1
ITEM	NAME OF PART	MATERIAL	NOTES	Q"TY
DWG	Marvin Zhang	DATE 2019.01.15	UNITS: MM	SHEET: 1 OF 1
CHK	Marvin Zhang	DATE 2019.01.15	SCALE: NONE 4:1 (1:1)	REV: A
APP		DATE	TITLE: OSTOQ 7.62 Series	X. ±0.50
			Close type Right-angle (90D)	X.X ±0.30
			PART NO. OSTOQXX0151	X° ±1°
			DWG NO. OSTOQXX0151.dwg	

REV	SIGN	DESCRIPTION	CHK.	DATE



ON-SHORE TECHNOLOGY, INC.

