Part Number : 1200680169
Product Description : M12 Signal, A-Coded, Solid Body Splitter, 1 x 4 Poles Male to 2 x 4 Poles Female, Grey TPE Overmold
Series Number : 120068
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : 81590R



Documents and Resources

Drawings

1200680169_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	M12 Signal, A-Coded, Solid Body Splitter, 1 x 4 Poles Male to 2 x 4 Poles Female, Grey TPE Overmold
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Splitter - Solid Body
UPC	78678840158

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	24V DC

Physical

Drop Connector	Micro-Change (M12)
Drop Gender	N/A
Keyway	Single
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Male

Downloaded from Arrow.com.

Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	TPE
Material - Coupling Nut	Black Epoxy Coated Zinc
Net Weight	32.658/g
Poles	3 Female/4 Male
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-20° to +105°C

Downloaded from Arrow.com.