molex



Part Number : 1200878463
Product Description : Nano-Change (M8) to Micro-Change (M12) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 0.25mm² PVC Cable, 2.0m (6.56') Length
Series Number : 120087
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 484030E02M020

Documents and Resources

Drawings

1200878463_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Relevant
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Nano-Change (M8) to Micro-Change (M12) Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 0.25mm² PVC Cable, 2.0m (6.56') Length
IP Rating	IP68
Product Name	Micro-Change (M12),Nano-Change (M8)
Protocol	N/A
Type	Double Ended
UPC	78172532419

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	N/A
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black

Downloaded from Arrow.com.

Connector End A	Nano-Change (M8)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	None
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	84.278/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-30° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	N/A

Downloaded from Arrow.com.