




**Part Number :** [5015680707](#)  
**Product Description :** 1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Right-Angle, Surface Mount, Tin Plated, Inner Positive Lock, 7 Circuits, Natural  
**Series Number :** 501568  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles

---

**Documents and Resources**

**Drawings**

[5015680707\\_sd.pdf](#)

**3D Models and Design Files**

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[5015680707.dxf](#)

**Specifications**

[5013300000-AS-000.pdf](#)

[SPK-501568-001-001.pdf](#)

[5013300000-PS-001.pdf](#)

[5013301000-PS-001.pdf](#)

[5013301000-PS-CHI-001.pdf](#)

[PS-501568-001-001.pdf](#)

---

**Product Environment Compliance**

**Compliance**

|                    |                                                                                                         |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Compliant with Exemption 44; 33                                                                         |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                            |
| Low-Halogen Status | Not Low-Halogen per IEC                                                                                 |

|            |                                                |
|------------|------------------------------------------------|
|            | 61249-2-21                                     |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS    | Compliant per EU 2015/863                      |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

**Part Details**

**General**

|                |                                                                                                                                   |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                                            |
| Category       | PCB Headers and Receptacles                                                                                                       |
| Series         | 501568                                                                                                                            |
| Description    | 1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Right-Angle, Surface Mount, Tin Plated, Inner Positive Lock, 7 Circuits, Natural |
| Application    | Wire-to-Board                                                                                                                     |
| Component Type | PCB Header                                                                                                                        |
| Product Name   | Pico-Clasp                                                                                                                        |
| UPC            | 822348871834                                                                                                                      |

**Agency**

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

**Electrical**

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 1.0A             |
| Voltage - Maximum             | 100V AC (RMS)/DC |

## Physical

|                                |                       |
|--------------------------------|-----------------------|
| Breakaway                      | No                    |
| Circuits (Loaded)              | 7                     |
| Circuits (maximum)             | 7                     |
| Color - Resin                  | Natural               |
| Durability (mating cycles max) | 30                    |
| First Mate / Last Break        | No                    |
| Gender                         | Male                  |
| Glow-Wire Capable              | No                    |
| Lock to Mating Part            | Yes                   |
| Material - Metal               | Phosphor Bronze       |
| Material - Plating Mating      | Tin                   |
| Material - Plating Termination | Tin                   |
| Material - Resin               | Nylon                 |
| Net Weight                     | 167.990/mg            |
| Number of Rows                 | 1                     |
| Orientation                    | Right Angle           |
| Packaging Type                 | Embossed Tape on Reel |
| PCB Locator                    | No                    |
| PCB Retention                  | Yes                   |
| Pitch - Mating Interface       | 1.00mm                |
| Pitch - Termination Interface  | 1.00mm                |
| Plating min - Mating           | 1.000µm               |
| Plating min - Termination      | 1.000µm               |
| Polarized to Mating Part       | Yes                   |
| Polarized to PCB               | No                    |
| Shrouded                       | Shrouded              |
| Stackable                      | No                    |
| Temperature Range - Operating  | -40° to +105°C        |
| Termination Interface Style    | Surface Mount         |

---

## Mates With / Use With

**Mates with Part(s)**

| Description                                           | Part Number   |
|-------------------------------------------------------|---------------|
| Pico-Clasp Low-Halogen Single Row Receptacle Housings | <u>501330</u> |

---

This document was generated on Jun 11, 2026