


Product Construction: 14 Conductor Cable Shielded and Jacketed	Product Description VG 95218 T028 C056 (EPD94266*)	Issue A S'sedes
--	--	--------------------

Designer Janice Campbell	Date 25/01/2002	Product Manager Martyn Cook	Date 25/01/2002	Page 1 of 1
------------------------------------	--------------------	---------------------------------------	--------------------	----------------



Controlled Customer Copy

B. W. B.
GERMANY

Specifications

VG 95218 Part 28 Type C

The copyright in this drawing is the property of Tyco Electronics UK Limited. The drawing is issued on condition it is not copied, reproduced or disclosed to a third party either in whole or in part without prior written consent of Tyco Electronics UK Limited.

Layer Type / Operation	Component Details Part Numbers refer to issue in effect at date of issue of this EPD.	Nominal O.D. mm
Components: Cable Cable Cable	1 of VG 95218 T023 G004 (Colour 0/1) 2 of VG 95218 T023 G005 (Colour 0/6) 4 of VG 95218 T023 G006 (Colour 0/8) Colours as above	
Cabling: Centre Layer 1	1 of VG 95218 T023 G005 1 of VG 95218 T023 G004 1 of VG 95218 T023 G005 4 of VG 95218 T023 G006 Fillers	9.1
Wrap:	Mylar	9.2
Shield: Optimised Braid	Tin Plated Copper	9.9
Jacket: Extrusion 1	Zerohal* – Black. Marked 'Raychem – VG 95218 T028 C056 – K1010 – VDE Reg.Nr. 7095 – LFMSGSGO (7x2x0.4)' (7x2x0.4)'	11.5 ±0.5 0.80mm minimum wall
Maximum Surface Transfer Impedance 50 milli ohms/metre 45 mΩ/metre @ 30MHz 30 mΩ/metre @ 10MHz	Notes Braid – AWG34 * – Raychem Trademark	Calculated nominal Maximum 253

If printed this document is an uncontrolled copy and reflects the issue status of the document on 26/10/2005 18:35

Lengths: Unless otherwise specified on your order this cable may be supplied in the following maximum number of continuous lengths:

Order Quantity (m) + One other length
100

Tyco Electronics UK Ltd
Faraday Road, Dorcan
Swindon SN3 5HH
Tel: (01793) 528171
Telex: 449409

Registration Number:
550926 London, England