

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

8.50 $\pm$.062
[216 $\pm$ 1.6]

1.00 $\pm$.062
[25.4 $\pm$ 1.57]
TYP. 2 PLCS.

4.00 $\pm$.062 [101.6 $\pm$ 1.6]
TYP. 2 PLCS.

11.00 $\pm$.062 [279.4 $\pm$ 1.6]

1.00 $\pm$.062
[25.4 $\pm$ 1.57]
TYP. 7 PLCS.

WHITE IMPRINT AREA

CLEAR AREA

PART NUMBER	MATERIAL	MARKER SIZE inches [mm]	LABELS PER SHEET	SHEET QTY.	STANDARD PKG. QTY.
S100X400YAJ	GYM6 CLEAR POLYESTER FILM	1.000 [25.4] X 4.000 [101.6]	14	72	1000

CAD FILENAME/LAYERS 100472CG_DC_C10207/02C

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING OPTIMUMM SELF-LAM.
LASER INKJET PRINTABLE LABELS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) $\pm$.12 (.XXX) $\pm$.025
(.XX) $\pm$.062 ANGLES $\pm$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY RVU
DATE 9/22/04
CHK'D

MAT'L:
SEE TABLE

SCALE NTS

DRAWING NO. C10207

DWG SIZE A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
2	10/29/09	RVU		UPDATE ON TOLERANCES. ADD +/- .062.	5898	R		
1	8/12/08	RVU		CHG. FORMAT FROM 'B' TO 'A' SIZE. TITLE AREA TOL. INCORRECT.	5516	R		
0	6-29-06	RVU		DRAWING RELEASE. MAT'L WAS GMY2.	4568	R		
A	9-22-04	RVU		ENGRG. RELEASE.	0000	R		