



+ CONNECTORS

TRANSISTOR SOCKETS



✓ Active

TE CONNECTIVITY (TE)
8058-1G31=TO5 SOCKET 230 CIRC

Augat | AD

8058-1G31
TE Internal Number: 1-1437508-5

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Number of Positions 10

Profile Low

Package TO-5

Lead Size Accepted .41 mm [.016 in]

Termination Method Printed Circuit

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

SOCKET, 8 PIN PRINTED CIRCUIT

PDF (TIFF AVAILABLE)

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminal Configuration Contact

Profile Low

Package TO-5

Product Type Socket

Configuration Features

Number of Positions 10

Body Features

Lead Size Accepted .41 mm [.016 in]

Color Black

Insulator Material Fluoropolymer

Sleeve Plating Material Gold

Sleeve Material Brass

Contact Features

Terminal Plating Gold

Termination Method Printed Circuit

Pin Diameter 5.84 mm [.23 in]

Terminal Material Beryllium Copper

Socket Type Transistor

Usage Conditions

Operating Temperature Range (°C) -55 – 125

Industry Standards

Insulator Flammability Rating UL 94V-0

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

