


REV.	DATE	DESCRIPTION
A	10/08/03	MODIFY PART DIMENSIONS / UPDATE DRAWING FORMAT
B	01/24/06	ADD FLAT ON BODY THREAD AREA



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS; DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex								
7	INSULATOR	TEFLON	NATURAL	1		DRAWN	G.R.S.	01/24/06										
6	HEX NUT	BRASS	NICKEL	1		CHECKED			PART DESCRIPTION BNC BULKHEAD DIRECT SOLDER JACK (FOR .085”, .086” CABLE)									
5	LOCK WASHER	BRASS	NICKEL	1		ISSUED												
4	GASKET	RUBBER	RED	1		SHEET	1 OF 1											
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	DO NOT SCALE DRAWING		CAD FILE		DWG. NO.		112580.DWG		REV. B		SIZE A		SCALE NA	
2	INSULATOR	TEFLON	NATURAL	1			C:/112/112580.DWG											
1	BODY	BRASS	NICKEL	1														
DESCRIPTION		MATERIAL	FINISH	QTY														