




FLEXSTRIP* JUMPERS

†CONDUCTOR PITCH "A"	MARGIN C (min.)		THICKNESS D (MAX.)		PIN DIAMETER E ±0,025 (±0.001")		NUMBER OF CONDUCTORS	
							min.	max.
Cat. Ref.	mm	(inch)	mm	(inch)	mm	(inch)		
1	1,27	.050"	0,25	.010"	0,64	.025"	2	30
6	1,90	.075"	0,38	.015"	0,84	.033"	2	30
2	2,54	.100"	0,51	.020"	0,84	.033"	2	30
3	3,18	.125"	1,52	.060"	0,84	.033"	2	25
4	3,81	.150"	1,52	.060"	0,84	.033"	2	20
5	5,08	.200"	1,52	.060"	0,84	.033"	2	15

2/86



Dimensions are shown in mm (inches.)
†Tolerance on Pitch ±0,25 (0.01") non-cumulative.

INSULATION LENGTH B ±1.57 (±0.062")		
mm	(inch)	Cat. Ref.
25.4	1	1
38.1	1½	1.5
50.8	2	2
63.5	2½	2.5
76.2	3	3
88.9	3½	3.5
101.6	4	4
114.3	4½	4.5
127	5	5
139.7	5½	5.5
152.4	6	6


PROPERTIES :-

Insulation Material - Nomex#
Temperature Rating - 105°C
Current Rating - 2 amps
U.L. Style Number - 5188

NOTES:-

*Trademark of Thomas & Betts Corporation
* Registered trademark of E.I. Du Pont de Nemours

CATALOGUE NUMBERING SYSTEM



EXAMPLE:-


FSN -22A - 15

FSN - Flexstrip Jumper With Nomex Insulation
2 - Conductor Pitch 2.54 (0.100)
2 - Insulation Length 50.8 (2)
A - Straight Pin
15 - Number of Conductors 15

T&B THOMAS & BETTS INTERNATIONAL
EUROPEAN ENGINEERING DIVISION

DRG. N°
3S-10018

IMPERIAL DIMENSIONS
SHOWN THUS []
TOLERANCES
-0000 EQUALS ± .0002
-000 EQUALS ± .003
-00 EQUALS ± .015



THIRD ANGLE PROJECTION

				MATERIAL	PART NAME
				HEAT TREAT	
				FINISH	PRODUCT CODE
				SCALE	TOLERANCES UNLESS OTHERWISE SPECIFIED
				DR.	FSN-22A-4
				CH.	
				APP.	
					tyco 5-1437142-9
					Electronics REV 0 SH720F1
REV		DESCRIPTION	DATE	BY	