

> You are here > Home > Products > ASSY FM CW COIL DF 4-ROW 20-CKT W/BAFFLE

Share:

f

+

ASSY FM CW COIL DF 4-ROW 20-CKT W/BAFFLE

0M-6422

★★★★★

Be the first to [write a review](#)

ASSY FM CW COIL DF 4-ROW 20-CKT W/BAFFLE

Not available in United States, call for more information

Product Support

?

Product FAQs

✓

Product Registration

Product Overview	Technical Specifications	Ratings & Reviews
NetworkAIR FM Features & Benefits		
Serviceability		
Front service access	The system has full service, front access for routine servicing of components. Front access also narrows the footprint of the system making it possible for units to be placed side by side.	
Availability		
Variable frequency drives	Enables the fans to be soft started, saving energy during power up. Controlling the motor speed simplifies the adjustment for static pressure and gives the option of back-draft prevention.	
Direct drive motors	Stress on bearings is nearly eliminated, increasing useful life. Allows integral fan/motor assembly to be factory balanced, which lowers vibration and expedites startup.	
Steam humidifier	Humidity is managed through a self-contained steam canister humidifier for maximum efficiency and ease of maintenance. The pure-steam canister maintains consistent capacity output, and requires very little scheduled maintenance.	
Tandem scroll compressors	Quiet and efficient operation of scroll compressors, connected on a common circuit for staged capacity control (N/A chilled water systems).	
Manageability		
Dew point humidity control	Humidification control can be set to dew point control instead of relative humidity control. Warmer return air temperatures can result in over-humidification when set for relative humidity control. Dew point control uses the moisture content of the air for humidification demand.	
Programmable input/output contacts	Allows device contacts to be connected to the air conditioner and mapped to customer outputs or system alarms.	
Network interface	Provides management by connecting the device directly to the network with a dedicated IP address, avoiding the need for a proxy such as a server. Management is available via Web browser, Telnet or SSH. Notification features inform you of problems as they occur.	
Microprocessor controller	Provides proactive control and real-time monitoring via a four line, eighty character, alphanumeric display.	
Redundant group control	Allows up to 4 groups of precision air conditioners to communicate with each other for redundancy, demand fighting prevention, mode assist, and global sharing of certain settings.	
Protection		
Double-walled panels	Separates insulation from the air stream, which prevents periodic maintenance of the insulation and reduces noise levels. Small particles of insulation can be picked up by the air stream if not isolated.	
Downloaded from Arrow.com		~ dirt and other particulates from the intake air for cleaner supply air.

SCR electric reheat

Modulates capacity to save energy. Exacting amounts of reheat loaded equally on all three phases.

Dedicated dehumidification

Boosts system efficiency by adding latent capacity without overcooling or increasing the requirement for reheat (N/A chilled water systems).

Product Distribution

Andorra , United Arab Emirates , Afghanistan , Antigua and Barbuda , Anguilla , Albania , Armenia , Netherlands Antilles , Angola , Argentina , Austria , Australia , Aruba , Azerbaijan , Bosnia and Herzegovina , Barbados , Bangladesh , Belgium , Burkina Faso , Bulgaria , Bahrain , Burundi , Benin , Bermuda , Brunei , Bolivia , Brazil , Bhutan , Botswana , Belarus , Belize , Canada , Central African Republic , Congo , Switzerland , Côte d'Ivoire , Cook Islands , Chile , Cameroon , China , Colombia , Costa Rica , Serbia and Montenegro , Cuba , Cyprus , Czech Republic , Germany , Djibouti , Denmark , Dominican Republic , Algeria , Ecuador , Estonia , Egypt , Western Sahara , Spain , Ethiopia , Finland , Fiji , Falkland Islands , France , Gabon , United Kingdom , Georgia , Ghana , Gibraltar , Gambia , Guinea , Equatorial Guinea , Greece , Guatemala , Guyana , Hong Kong , Honduras , Croatia , Hungary , Indonesia , Ireland , Israel , India , Iraq , Iran , Iceland , Italy , Jamaica , Jordan , Japan , Kenya , Cambodia , South Korea , Kuwait , Cayman Islands , Kazakhstan , Lebanon , Liechtenstein , Sri Lanka , Liberia , Lesotho , Lithuania , Luxembourg , Latvia , Morocco , Moldova , Macedonia , Mali , Myanmar , Mauritania , Malta , Malawi , Mexico , Malaysia , Mozambique , Namibia , Niger , Nigeria , Nicaragua , Netherlands , Norway , Nepal , New Zealand , Oman , Panama , Peru , Papua New Guinea , Philippines , Pakistan , Poland , Puerto Rico , Portugal , Paraguay , Romania , Russia , Rwanda , Saudi Arabia , Sudan , Sweden , Singapore , Slovenia , Slovakia , Sierra Leone , Senegal , Somalia , El Salvador , Chad , Togo , Thailand , Turkmenistan , TP , Turkey , Trinidad and Tobago , Taiwan , Tanzania , Ukraine , Uganda , United States , Uruguay , Uzbekistan , Venezuela , U.S. Virgin Islands , Vietnam , Yemen , South Africa , Zambia , ZR , Zimbabwe

Life Is On



Sign up to stay up to date with best practices, new solutions and special offers.

WHO WE ARE

[About APC](#)
[Investor Relations](#)
[Careers](#)
[Sustainability](#)

CONNECT WITH US

[Press](#)
[APC Blog](#)
[Schneider Electric Data Center Blog](#)
[Contact Us](#)
[Rate this website](#)

FIND A RESELLER

CATALOG KEYCODE

