



Polyamide braided sleeving for excellent abrasion resistance

Helagaine HEGPA66

Helagaine HEGPA66 is particularly suitable for vehicle manufacturing as well as plant construction.

Features and Benefits

- Made from heavy-duty polyamide yarn
- Excellent abrasion resistance
- Highly flexible
- Easy to apply over irregular shapes
- Eases application by expanding when compressed
- Very high surface covering



Various types of Helagaine braided sleeving.

MATERIAL	Polyamide 6.6 (PA66)
Operating Temperature	-60 °C to +150 °C, intermittent +200 °C
Melting Point	+255 °C
Flammability	UL94 V2, FMVSS 302
Specifications	EN 45545: 2013

HF

RoHS



To prevent fraying, the sleeve can be cut with the hot cutting tool HSG0. See page 533.

TYPE	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Article-No.
HEGPA6604	3.0	6.0	Black (BK)	200 m	170-40400
HEGPA6606	4.0	8.0	Black (BK)	100 m	170-40600
HEGPA6608	5.0	10.0	Black (BK)	100 m	170-40800
HEGPA6610	7.0	12.0	Black (BK)	100 m	170-41000
HEGPA6612	8.0	14.0	Black (BK)	100 m	170-41200
HEGPA6616	12.0	18.0	Black (BK)	50 m	170-41600
HEGPA6620	15.0	23.0	Black (BK)	50 m	170-42000
HEGPA6625	18.0	28.0	Black (BK)	50 m	170-42500
HEGPA6630	25.0	32.0	Black (BK)	50 m	170-43000
HEGPA6640	30.0	44.0	Black (BK)	50 m	170-44000
HEGPA6650	40.0	55.0	Black (BK)	50 m	170-45000
HEGPA6660	50.0	65.0	Black (BK)	50 m	170-46000

All dimensions in mm. Subject to technical changes.

Colour grey available on request. Cuts in any lengths. Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.