

LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED PER ECO-08-007327			05SEP08	BM	WM





1 .THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.

2 DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.

3 MATERIAL: HOUSING – POLYPHENYLENE OXIDE, BLACK. TERMINAL – HIGH STRENGTH COPPER ALLOY PLATED WITH 0.76μm [.000030] MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL, 0.76μm [.000030] MIN TOTAL ON MATING SURFACE, OVER 1.27μm [.000050] MIN NICKEL UNDERPLATE OF ENTIRE TERMINAL.

4 CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF AMP INCORPORATED.

5 .WIRE SIZE: 24 & 26 AWG SOLID & 24 AWG 7 STRAND COPPER CONDUCTORS. MAXIMUM INSULATION DIAMETER OF 1.15[.045] IS ACCEPTABLE FOR MOST APPLICATIONS.



1116549-1  
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DL DRUMMOND 19-MAR-99	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK DL DRUMMOND 22-MAR-99	NAME PLUG ASSEMBLY, 50 POSITION,B-SLOT,WITH M3 THREADS	
		APVD AM FLETCHER 22-MAR-99	PRODUCT SPEC	
			APPLICATION SPEC	
			RESTRICTED TO	
MATERIAL		FINISH	SIZE A1	CAGE CODE 00779
			DRAWING NO 1116549	REV C
			WEIGHT	SCALE 4:1
			CUSTOMER DRAWING	SHEET 1 OF 1