

"P" ORDER

RELEASE NO. PR-17287

CHECK

CHECK

JAP

CHECK

WJM

29 AUG 89

SEP 89

41AC1-1

M

DRAWING  
NUMBER

3


ISSUE

REVISIONS  
A REL DWG  
PR17287  
WJM  
29 AUG 89

DDM/CAD

DRAWN

PUSH TO OPERATE — RETURNS  
AUTOMATICALLY TO POSITION SHOWN  
PULL TO OPERATE — REMAINS IN  
OPERATED POSITION UNTIL RESET  
FOR AUTOMATIC RETURN BY NEXT  
FULL STROKE "PUSH" OPERATION




NOTES

- 1 — UNIT INCLUDES CATALOG LISTING "12SE" TYPE BASIC SWITCH (2)
- 2 — NOTCH IN ACTUATOR ROD WILL PERMIT .035 DISPLACEMENT BETWEEN END OF ROD AND HOLE IN BRACKET
- 3 — SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

TOTAL TRAVEL — — — .250 APPROX  
PUSH DIRECTION  
  
.188 APPROX  
PULL DIRECTION

ELECTRICAL DATA

CONTACT ARRANGEMENT  
S P D T (2)

250 VAC — — — — — 5 AMP  
  
30 VOLTS DC RATING  
INDUCTIVE — — — SEA LEVEL — — — 3 AMP  
50,000 FT — — — 2.5 AMP  
RESISTIVE — — — SEA LEVEL — — — 5 AMP  
50,000 FT — — — 5 AMP  
MAXIMUM INRUSH — — — — — 24 AMP

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED  
TOLERANCES ARE  
ONE PLACE (.0) ± .030  
TWO PLACE (.00) ± .015  
THREE PLACE (.000) ± .005  
ANGLES ±  
WEIGHT