

Preliminary TS278RL00 Series

2A Ultra Low Dropout Voltage Regulator w/Disable

ITO-220-4L



Pin Definition:

1. Input
2. Output
3. Ground
4. Enable

General Description

The TS278RL00 Series is a low-dropout voltage regulator suitable for various electronic equipments. It provides constant voltage power source with ITO-220 4 lead full mold package.

Dropout voltage of TS278RL00 Series is below 0.5V in full rated current (2A). This regulator has various functions such as a peak current protection, thermal shut down, over voltage protection and an output disable function.

Features

- Ultra Low Dropout performance 0.5Vmax. 2A
- Over Current Protection, Thermal Shutdown
- Over Voltage Protection, Short Circuit Protection
- With Output Disable Function
- $\pm 2.4\%$ Typical Total output
- TO-220 Full-Mold Package (4Pin)


Ordering Information

Part No.	Package	Packing
TS278RL xx CI4 C0	ITO-220-4L	50pcs / Tube

Note: Where ~~xx~~ denotes voltage option,

33=3.3V, **05**=5V, **08**=8V, **09**=9V, **12**=12V, **15**=15V

Block Diagram



Preliminary **TS278RL00 Series**

2A Ultra Low Dropout Voltage Regulator w/Disable

Absolute Maximum Rating

Parameter	Symbol	Value	Unit	Remark
Input Voltage	V_{IN}	18	V	--
Disable Voltage	V_{DIS}	18	V	--
Output Current	I_O	2	A	--
Power Dissipation 1	P_D 1	1.5	W	No heat sink
Power Dissipation 2	P_D 2	15	W	With heat sink
Junction Temperature	T_J	-40~+125	°C	--
Thermal Resistance, Junction-to Case (Note2)	$R\theta_{JC}$	4.31	°C / W	--
Thermal Resistance, Junction-to Air (Note2)	$R\theta_{JA}$	48.83	°C / W	--
Thermal Shutdown Temperature (Junction)	T_{SD}	150	°C	--

Electrical Specifications (V_{IN} =Note 6, I_O =1.0A, T_a =25°C, unless otherwise specified).

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Output Voltage	TS278RL33	V_O	3.22	3.3	3.38	V
	TS278RL05		4.88	5.0	5.12	
	TS278RL08		7.80	8.0	8.20	
	TS278RL09		8.78	9.0	9.22	
	TS278RL12		11.71	12	12.28	
	TS278RL15		14.64	15	15.36	
Load Regulation	REG_{LOAD}	I_O =5mA~2A	--	0.1	2.0	%
Line Regulation	REG_{LINE}	Note 7	--	0.5	2.5	%
Ripple Rejection Ratio	RR	Note1	45	55	--	dB
Dropout Voltage	V_{DROP}	I_O =2A	--	--	0.5	V
Disable Voltage High	V_{DIS} H	Output Active	2.0	--	--	V
Disable Voltage Low	V_{DIS} L	Output Disabled	--	--	0.8	V
Disable Bias Current High	I_{DIS} H	V_{DIS} =2.7V	--	--	20	uA
Disable Bias Current Low	I_{DIS} L	V_{DIS} =0.4V	--	--	-0.4	mA
Quiescent Current	I_q	I_O =0A	--	--	10	mA


Note:

1. These parameters, although guaranteed, are not 100% tested in production.
2. Junction -to -case thermal resistance test environments.
3. Pneumatic heat sink fixture.
4. Clamping pressure 60psi through 12mm diameter cylinder.
5. Thermal grease applied between PKG and heat sink fixture
6. TS278RL33: V_{IN} =5V, TS278RL05: V_{IN} =7V, TS278RL08: V_{IN} =10V, TS278RL09: V_{IN} =11V, TS278RL12: V_{IN} =15V, TS278RL15: V_{IN} =18V
7. TS278RL33: V_{IN} =4~10V, TS278RL05: V_{IN} =6~12V, TS278RL08: V_{IN} =9~18V, TS278RL09: V_{IN} =10~18V, TS278RL12: V_{IN} =13~18V, TS278RL15: V_{IN} =16~18V


Preliminary TS278RL00 Series

2A Ultra Low Dropout Voltage Regulator w/Disable


Standard Test Circuit



Ripple Rejection Test Circuit




Standard Application Circuit



Preliminary TS278RL00 Series


2A Ultra Low Dropout Voltage Regulator w/Disable

ITO-220-4L Mechanical Drawing



ITO-220-4L DIMENSION				
DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	4.42	4.72	0.174	0.186
A1	2.69	2.89	0.136	0.114
A2	1.68	1.88	0.066	0.074
D	10.00	10.20	0.394	0.402
E	6.85	7.05	0.269	0.278
E1	8.54	8.74	0.336	0.344
L	13.15	13.55	0.518	0.533
L2	16.56	16.76	0.652	0.660
L2	3.60	3.80	0.142	0.150
He	28.44	28.92	1.119	1.159
C	0.48		0.019	
E	2.54(TYP)		0.1(TYP)	
b	0.635(TYP)		0.025(TYP)	
θ	4°	7°	4°	7°

Marking Diagram



- XX** = Voltage Code
(33=3.3V, 05=5V, 08=8V, 09=9V, 12=12V, 15=15V)
- Y** = Year Code
- M** = Month Code
(A=Jan, B=Feb, C=Mar, D=Apr, E=May, F=Jun, G=Jul, H=Aug, I=Sep, J=Oct, K=Nov, L=Dec)
- L** = Lot Code
- CI4** = Package Code for Adjustable type
(CI4 = ITO-220-4L)

Preliminary TS278RL00 Series

2A Ultra Low Dropout Voltage Regulator w/Disable

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.