

# LP Series Miniature Snap-in Slide Switches

## Features/Benefits

- **6 to 11 AMPS available**
- **Easy assembly—Snap-in mounting**
- **Contamination resistant—extended actuator**
- **Positive detent**
- **RoHS compliant**

## Typical Applications

- **Small appliances**
- **Outdoor appliances**
- **Portable tools**



Models Available

## Specifications

CONTACT RATING: Q contact material (LP0X, LP2X Models: 6 AMPS @ 125 V AC or 28 V DC; 3 AMPS @ 250 V AC (UL/CSA). (LP7X, LP8X Models): 11 AMPS @ 125/250 V AC (UL/CSA). See page I-27 for additional ratings.

ELECTRICAL LIFE: 10,000 make-and-break cycles at full load.

INSULATION RESISTANCE:  $10^9 \Omega$  min.

DIELECTRIC STRENGTH: 1,000 Vrms min. @ sea level.

CONTACT RESISTANCE: Below 10 m  $\Omega$  typ. initial  
@ 2-4 V DC, 100 mA, for both silver and gold plated contacts.

OPERATING TEMPERATURE: -30°C to +65°C

STORAGE TEMPERATURE: -30°C to +85°C

**NOTE:** Any models supplied with Q, B or G contact material are RoHS compliant.

**NOTE:** Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

## Materials

HOUSING: 6/6 nylon (UL94V-2), black.

ACTUATOR: Glass filled acetal, UV and petroleum resistant, black.

CONTACTS: Q contact material: Copper, silver plated. See page I-27 for additional contact materials.

TERMINALS: Q contact material: Copper, silver plated. See page I-27 for additional contact materials.

CONTACT SPRING: Music wire or stainless steel.



TERMINAL SEAL: Epoxy.



Slide

## Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages I-26 and I-27. For additional options not shown in catalog, consult Customer Service Center.



Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change

[www.ck-components.com](http://www.ck-components.com)




# LP Series

## Miniature Snap-in Slide Switches

### SWITCH FUNCTION



NO. POLES	MODEL NO.	AMP RATING*	SWITCH FUNCTION	SCHEMATIC
SP	LP02	6	SPDT	







All models **C&K** us with all options when ordered with 'Q' contact material.

Contacts make on side actuator thrown.

\* For complete contact ratings, see CONTACT MATERIALS Section, page I-27.

Slide

NO. POLES	MODEL NO.	AMP RATING*	SWITCH FUNCTION	SCHEMATIC
DP	LP22	6	DPDT	
	LP81	11	DPST	
	LP82	11	DPDT	




Part number shown: LP22C21S203Q

Terminal Nos.  
For Reference Only

### ACTUATOR



#### C1; C2; C3



OPTION CODE2	ACTUATOR CAP COLOR
C2	BLACK
C1	WHITE
C3	RED

NOTE: Actuator finish: gloss.  
Other colors available,  
consult Customer Service Center.

### DETENT



#### 1 WITH DETENT

### MOUNTING STYLE




#### T2 SNAP-IN PANEL WITH TABS



Mounting style T2 suitable for markings.  
See HOUSING MARKINGS options.

PANEL THICKNESS	DIM 'A'
.030-.045 (0.76) (1.14)	.578 (14.68)
.046-.059 (1.17) (1.50)	.585 (14.86)
.060-.089 (1.52) (2.26)	.598 (15.19)
.090-.120 (2.29) (3.05)	.610 (15.49)

#### PANEL MOUNTING



Dimensions are shown: Inch (mm)  
Specifications and dimensions subject to change




[www.ck-components.com](http://www.ck-components.com)

# LP Series Miniature Snap-in Slide Switches

## TERMINATIONS





**03** SOLDER LUG WITH HOLE



## HOUSING MARKINGS

**NONE** NO MARKINGS

**D** ON-OFF



**NOTE:** Housing markings are available with 'T2' mounting style only. The marking color on all housings with marking options 'D' is white, standard. Other marking colors are available, consult Customer Service Center.

Orientation of actuator and terminals.

## CONTACT MATERIAL

OPTION CODE	CONTACT MATERIAL	RATINGS	
<b>Q</b>	SILVER <sup>2</sup>	POWER	LPOX, LP2X MODELS: 6 AMPS @ 125 V AC or 28 V DC; 3 AMPS @ 250 V AC (UL/CSA). LP7X, LP8X MODELS: 11 AMPS @ 125/250 V AC (UL/CSA).
<b>B</b>	GOLD <sup>1</sup>	LOW LEVEL/DRY CIRCUIT	0.4 VA MAX. @20 V AC OR DC MAX.

\* Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.


<sup>1</sup> CONTACTS & TERMINALS: Copper, with gold plate over nickel plate.

**NOTE:** Any models supplied with Q or B contact material are RoHS compliant.

<sup>2</sup> CONTACTS & TERMINALS: Copper, silver plated (standard with all termination options).

All models  with all when ordered with 'Q' contact material.

<sup>3</sup> CONTACTS & TERMINALS: Copper, with gold plate over nickel plate over silver plate.



Dimensions are shown: Inches (mm)  
Specifications and dimensions subject to change



[www.ck-components.com](http://www.ck-components.com)