


500 W, 50 V, 700 to 1200 MHz RF power LDMOS transistor



STAC780-4F

Features

Order code	F _{REQ}	V _{DD}	P _{OUT} typ.	G _{ain}	N _D
STAC1011-500	1030 to 1090 MHz	50 V	500 W	16 dB	59%

- High efficiency and linear gain operations
- Integrated ESD protection
- Internal input matching for ease of use
- Large positive and negative gate/source voltage range for improved class C operation
- In compliance with the European Directive 2002/95/EC

Applications

- Avionics

Description

The STAC1011-500 is a 50 V common-source N-channel enhancement-mode lateral field-effect RF power transistor designed for avionics applications at frequencies up to 1250 MHz.



Product status link

[STAC1011-500](#)

Product summary

Order code	STAC1011-500
Marking	1011-500 ES
Package	STAC780-4F
Packing	TBD

1 Electrical ratings

Table 1. Absolute maximum ratings (+25 °C)

Symbol	Parameter	Value	Unit
B_{VDS}	Drain-source voltage	110	V
V_{GS}	Gate-source voltage	-8/+10	V
V_{DD}	Drain supply voltage	50	V
T_{STG}	Storage temperature range	-65 to +150	°C
T_J	Junction temperature	+200	°C

Table 2. Thermal data

Symbol	Parameter	Value	Unit
$R_{thj-case}$	Junction-case thermal resistance $T_{CASE} = +85\text{ °C}$, $T_J = +200\text{ °C}$, DC test	TBD	°C/W

Table 3. ESD protection

Symbol	Parameter	Class
HBM	Human body model (according to JESD22-A114)	2

2 Electrical characteristics

($T_C = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)

Table 4. Static (per side)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)DSS}$	Drain-source breakdown voltage	$V_{GS} = 0\text{ V}$, $I_D = 100\text{ }\mu\text{A}$	110			V
I_{DSS}	Zero-gate voltage drain current	$V_{GS} = 0\text{ V}$, $V_{DS} = 50\text{ V}$			1	μA
I_{GSS}	Gate-body leakage current	$V_{DS} = 0\text{ V}$, $V_{GS} = 6\text{ V}$			1	μA
$V_{GS(th)}$	Gate threshold voltage	$V_{DS} = 50\text{ V}$, $I_D = 50\text{ mA}$	1.0		3.0	V
$V_{DS(on)}$	Static drain-source on-voltage	$V_{GS} = 10\text{ V}$, $I_D = 5\text{ A}$			1.4	V
C_{ISS}	Common source input capacitance	$V_{GS} = 0\text{ V}$, $V_{DD} = 50\text{ V}$, $F_{REQ} = 1\text{ MHz}$		TBD		pF
C_{RSS}	Common source feedback capacitance			2		pF
C_{OSS}	Common source output capacitance			44		pF

Table 5. Dynamic


Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
P_{OUT}	Output power	$V_{DD} = 50\text{ V}$, $I_{DQ} = 0.02\text{ A}$, $P_{in} = 14\text{ W}$, $F_{REQ} = 1030\text{ to }1090\text{ MHz}$	-	500	-	W
Gain	Power gain		-	16	-	dB
Efficiency	Drain efficiency		-	59	-	%
IMD3	3rd order intermodulation		-	TBD	-	dBc
VSWR	Load mismatch	$P_{OUT} = 500\text{ W}$, all phases	-	10:1	-	

Table 6. Impedance data

Frequency (in MHz)	Input impedance (Z_{IN})	Drain load impedance (Z_{DL})
1030	$1.527 + 1.687j$	$1.451 - 0.115j$
1060	$1.376 + 1.128j$	$1.436 - 0.186j$
1090	$1.266 - 0.570j$	$1.389 - 0.256j$


2.1 Electrical characteristics (curves)

Figure 1. Power gain vs output power



GADG060920181242IG

Figure 2. Drain efficiency vs output power




GADG060920181239IG

3 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

3.1 STAC780-4F package information

Figure 3. STAC780-4F package outline



PIN	CONNECTIO N
1	DRAIN
2	SOURCE
3	GATE

DM00481940-1

Table 7. STAC780-4F mechanical data

Ref.	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	3.76		3.86	0.148		0.152
A1	5.03		5.13	0.198		0.202
B	4.57		5.08	0.180		0.200
C	9.65		9.91	0.380		0.390
D	20.17		20.37	0.794		0.802
E	20.45		20.70	0.805		0.815
F	0.11		0.17	0.005		0.007
G	0.97		1.14	0.038		0.045
H	1.52		1.70	0.060		0.067
I	3.18		4.32	0.125		0.170
J	9.52		9.78	0.375		0.385
q		1.37			0.057	
r		1.52			0.060	
s		0.51			0.020	
CH1		2.03			0.08	

Revision history

Table 8. Document revision history

Date	Version	Changes
06-Sep-2018	1	Initial release
22-Mar-2019	2	Updated Table 4 .
26-Sep-2019	3	Changed silhouette on cover page.

Contents

1	Electrical ratings	2
2	Electrical characteristics.....	3
2.1	Electrical characteristics (curves)	4
3	Package information.....	5
3.1	STAC780-4F package information	5
	Revision history	7

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics – All rights reserved