


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A2	NEW RELEASE	22/JUNE/2022	
A3	CHANGE CABLE PRINTING	28/JULY/2025	



CABLE PRINTING: Amphenol Cables on Demand E119932-Y AWM 2464 80°C 300V  
26AWG VW-1 LL84201 CSA AWM I/II A 80°C 300V 26AWG FT1 COPARTNER



PIN OUT

P1	P2	P1	P2
1	1	20	20
2	2	21	21
3	3	22	22
4	4	23	23
5	5	24	24
6	6	25	25
7	7	26	26
8	8	27	27
9	9	28	28
10	10	29	29
11	11	30	30
12	12	31	31
13	13	32	32
14	14	33	33
15	15	34	34
16	16	35	35
17	17	36	36
18	18	37	37
19	19	SHELL	SHELL DRAIN WIRE

NOTE:  
 1. TESTING CONDITIONS:  
 A: INSULATION RESISTANCE: 10MΩ  
 B: VOLTAGE: DC300V/0.01S  
 C: CONDUCTOR RESISTANCE 2Ω(≤3M), 5Ω(>3M,<10M), 8M≥10Ω  
 2. SHIELDING: COPPER FOIL TAPE COVER PREMOLD 360°, DRAIN WIRE SOLDER TO CONNECTOR SHELL

P/N CHART

ACD P/N	LENGTH ± T	
CS-DSDMDB37MF-002.5	2.5FT±1inch	762±25mm
CS-DSDMDB37MF-005	5FT±2inch	1524±51mm
CS-DSDMDB37MF-010	10FT±3inch	3048±76mm
CS-DSDMDB37MF-015	15FT±3inch	4572±76mm
CS-DSDMDB37MF-025	25FT±4inch	7620±102mm
CS-DSDMDB37MF-050	50FT±8inch	15240±203mm



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:

DECIMALS	ANGLES	EAR NO.	APPROVALS		DATE
X ±X	± X°		DRAWN	XF	
.XX ±.XX			CHECKED	HYJ	
.XXX ±.XXX			RESP ENG		
			MFG ENG		

THIRD ANGLE PROJECTION

Amphenol Cables on Demand  
20 VALLEY ST. ENDICOTT, NY 13760

CABLE, DB37 M/F MOLDED XX

SIZE A DWG. NO. CS-DSDMDB37MF-XXX REV. A3

CAD FILE: SCALE: N/A SHEET 1 OF 1

NOTES: UNLESS OTHERWISE SPECIFIED