


**SURFACE MOUNT  
UNIDIRECTIONAL AND BIDIRECTIONAL  
TRANSIENT VOLTAGE SUPPRESSORS**
**FEATURES**

- For surface mounted applications
- Reliable low cost construction utilizing molded plastic technique
- IR less than 0.5uA above 10V
- Fast response time: typically less than 1.0ns for Uni-direction less than 5.0ns for Bi-direction from 0 Volts to BV min
- Automotive grade
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- Halogen and Antimony Free. "Green" Device (Note 3)
- The ASMAJ SERIES are suitable for automotive applications requiring specific change control; these parts are AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.


<https://www.diodes.com/quality/product-definitions/>
**MECHANICAL DATA**

- Package: Molded plastic
- Package Material: Molding compound, UL Flammability classification 94V-0, (No Br. Sb. Cl.) "Halogen-free"
- Polarity: by cathode band denotes uni-directional device none cathode band denotes bi-directional device
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL STD-202, Method 208 e3
- Weight: 0.002 ounces, 0.064 gram (Approximate)

**STAND-OFF VOLTAGE - 5.0 to 100 Volts  
POWER DISSIPATION - 400 Watts**
**SMA**


SMA		
DIM.	MIN.	MAX.
A	4.06	4.57
B	2.29	2.92
C	1.27	1.63
D	0.15	0.31
E	4.83	5.59
F	0.05	0.20
G	1.96	2.40
H	0.76	1.52

All Dimensions in millimeter

**MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS**

Ratings at 25°C ambient temperature unless otherwise specified.

**ABSOLUTE RATINGS**

PARAMETER	SYMBOL	VALUE	UNIT
PEAK POWER DISSIPATION AT TA = 25 °C , TP = 1ms (Note 4)	P <sub>PK</sub>	400	W
Peak Forward Surge Current 8.3ms single half sine-wave @ TJ = 25 °C (Note 5)	I <sub>FSM</sub>	40	A
Steady State Power Dissipation, with PCB	P <sub>M(AV)</sub>	1.0	W
Maximum Instantaneous forward voltage at 16A (Notes 5, 6)	V <sub>F</sub>	3.0	V
Operating Temperature Range	T <sub>J</sub>	-55 to +175	°C
Storage Temperature Range	T <sub>STG</sub>	-55 to +175	°C

**Notes:**

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. Non-repetitive current pulse, per fig. 3 and derated above T<sub>A</sub> = 25 °C per fig.1.
5. For unidirectional units only.
6. VF max=3.0V at IF=16 A 300us square wave pulse. (for devices of VBR<100V)

## ELECTRICAL CHARACTERISTICS

Device Uni- Directional	Device Bi- Directional	Device Marking Code		Working Peak Reverse Voltage	Breakdown Voltage VBR Volts			Maximum Reverse Voltage at $I_{RSM}$ (Clamping Voltage)	Maximum Reverse Surge Current	Maximum Reverse Leakage at $V_{RWM}$
(UNI)	(BI)	(UNI)	(BI)	$V_{RWM}$ (V)	Min (V)	Max (V)	$I_t$ (mA)	$V_{RSM}$ (V)	$I_{RSM}$ (A)	IR (uA)
ASMAJ5.0A	ASMAJ5.0CA	AHE	ATE	5.0	6.40	7.07	10	9.2	43.5	800
ASMAJ6.0A	ASMAJ6.0CA	AHG	ATG	6.0	6.67	7.37	10	10.3	38.8	800
ASMAJ6.5A	ASMAJ6.5CA	AHK	ATK	6.5	7.22	7.98	10	11.2	35.7	500
ASMAJ7.0A	ASMAJ7.0CA	AHM	ATM	7.0	7.78	8.60	10	12.0	33.3	200
ASMAJ7.5A	ASMAJ7.5CA	AHP	ATP	7.5	8.33	9.21	1	12.9	31.0	100
ASMAJ8.0A	ASMAJ8.0CA	AHR	ATR	8.0	8.89	9.83	1	13.6	29.4	50
ASMAJ8.5A	ASMAJ8.5CA	AHT	ATT	8.5	9.44	10.43	1	14.4	27.7	10
ASMAJ9.0A	ASMAJ9.0CA	AHV	ATV	9.0	10.0	11.1	1	15.4	26.0	5
ASMAJ10A	ASMAJ10CA	AHX	ATX	10	11.1	12.3	1	17.0	23.5	5
ASMAJ11A	ASMAJ11CA	AHZ	ATZ	11	12.2	13.5	1	18.2	22.0	0.5
ASMAJ12A	ASMAJ12CA	AIE	AUE	12	13.3	14.7	1	19.9	20.1	0.5
ASMAJ13A	ASMAJ13CA	AIG	AUG	13	14.4	15.9	1	21.5	18.6	0.5
ASMAJ14A	ASMAJ14CA	AIK	AUK	14	15.6	17.2	1	23.2	17.2	0.5
ASMAJ15A	ASMAJ15CA	AIM	AUM	15	16.7	18.5	1	24.4	16.4	0.5
ASMAJ16A	ASMAJ16CA	AIP	AUP	16	17.8	19.7	1	26.0	15.3	0.5
ASMAJ17A	ASMAJ17CA	AIR	AUR	17	18.9	20.9	1	27.6	14.5	0.5
ASMAJ18A	ASMAJ18CA	AIT	AUT	18	20.0	22.1	1	29.2	13.7	0.5
ASMAJ20A	ASMAJ20CA	AIV	AUV	20	22.2	24.5	1	32.4	12.3	0.5
ASMAJ22A	ASMAJ22CA	AIX	AUX	22	24.4	27.0	1	35.5	11.2	0.5
ASMAJ24A	ASMAJ24CA	AIZ	AUZ	24	26.7	29.5	1	38.9	10.3	0.5
ASMAJ26A	ASMAJ26CA	AJE	AVE	26	28.9	31.9	1	42.1	9.5	0.5
ASMAJ28A	ASMAJ28CA	AJG	AVG	28	31.1	34.4	1	45.4	8.8	0.5
ASMAJ30A	ASMAJ30CA	AJK	AVK	30	33.3	36.8	1	48.4	8.3	0.5
ASMAJ33A	ASMAJ33CA	AJM	AVM	33	36.7	40.6	1	53.3	7.5	0.5
ASMAJ36A	ASMAJ36CA	AJP	AVP	36	40.0	44.2	1	58.1	6.9	0.5
ASMAJ40A	ASMAJ40CA	AJR	AVR	40	44.4	49.1	1	64.5	6.2	0.5
ASMAJ43A	ASMAJ43CA	AJT	AVT	43	47.8	52.8	1	69.4	5.7	0.5
ASMAJ45A	ASMAJ45CA	AVJ	AVV	45	50.0	55.3	1	72.7	5.5	0.5
ASMAJ48A	ASMAJ48CA	AJX	AVX	48	53.3	58.9	1	77.4	5.2	0.5
ASMAJ51A	ASMAJ51CA	AJZ	AVZ	51	56.7	62.7	1	82.4	4.9	0.5
ASMAJ54A	ASMAJ54CA	ARE	AWE	54	60.0	66.3	1	87.1	4.6	0.5
ASMAJ58A	ASMAJ58CA	ARG	AWG	58	64.4	71.2	1	93.6	4.3	0.5
ASMAJ60A	ASMAJ60CA	ARK	AWK	60	66.7	73.7	1	96.8	4.1	0.5
ASMAJ64A	ASMAJ64CA	ARM	AWM	64	71.1	78.6	1	103	3.9	0.5
ASMAJ70A	ASMAJ70CA	ARP	AWP	70	77.8	86.0	1	113	3.5	0.5
ASMAJ75A	ASMAJ75CA	ARR	AWR	75	83.3	92.1	1	121	3.3	0.5
ASMAJ78A	ASMAJ78CA	ART	AWT	78	86.7	95.8	1	126	3.2	0.5
ASMAJ85A	ASMAJ85CA	ARV	AWV	85	94.4	104	1	137	2.9	0.5
ASMAJ90A	ASMAJ90CA	ARX	AWX	90	100	111	1	146	2.7	0.5
ASMAJ100A	ASMAJ100CA	ARZ	AWZ	100	111	123	1	162	2.5	0.5







**Notes:**

Suffix 'A' denotes 5% tolerance device.

1.) Add suffix 'C' or ' CA' after part number to specify Bi-directional devices.

2.) The IR limit is double for Bi-Directional devices.

**RATING AND CHARACTERISTIC CURVES**  
**ASMAJ SERIES**



## Ordering Information :

Part Number	Package	Packing	
		Qty.	Carrier
ASMAJ SERIES	SMA	5000pcs	Reel

## Marking Information :




XXXX : Assembly Tracing code  
ZZZ : Product Type Marking code  
Bar Denotes Cathode Side

## Packaging Information :

DEVICE	Q'TY/REEL (PCS)	REEL DIA. (INCH)	Q'TY/BOX (PCS)	Q'TY/CARTON (PCS)
ASMAJXXA ASMAJXXCA	5000	13	10K	80K

## Suggested Pad Layout :



**Note:** The suggested land pattern dimensions have been provided for reference only, as actual pad layouts may vary depending on application. These dimensions may be modified based on user equipment capability or fabrication criteria. A more robust pattern may be desired for wave soldering and is calculated by adding 0.2 mm to the 'Z' dimension. For further information, please reference document IPC-7351A, Naming Convention for Standard SMT Land Patterns, and for International grid details, please see document IEC, Publication 97.

**Note:** For high voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking.

**IMPORTANT NOTICE**

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.  
All other trademarks are the property of their respective owners.  
© 2023 Diodes Incorporated. All Rights Reserved.

[www.diodes.com](http://www.diodes.com)