

ROHS COMPLIANT

PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
	SEE SHEET 1		

"XX" NUMBER TO dB VALUE CHART

"XX" NUMBER	dB VALUE		"XX" NUMBER	dB VALUE		"XX" NUMBER	dB VALUE		"XX" NUMBER	dB VALUE
01	1		19	19		43	17		72	7
02	2		20	20		44	18		73	7.5
03	3		27	1		45	19		74	8
04	4		28	2		46	20		75	8.5
05	5		29	3		58	0		76	9
06	6		30	4		59	0.5		77	9.5
07	7		31	5		60	1		78	10
08	8		32	6		61	1.5		79	11
09	9		33	7		62	2		80	12
10	10		34	8		63	2.5		81	13
11	11		35	9		64	3		82	14
12	12		36	10		65	3.5		83	15
13	13		37	11		66	4		84	16
14	14		38	12		67	4.5		85	17
15	15		39	13		68	5		86	18
16	16		40	14		69	5.5		87	19
17	17		41	15		70	6		88	20
18	18		42	16		71	6.5			

NOTES:

1. M3933/25-58 DOES NOT HAVE A RESISTIVE PATH TO GROUND.

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIED	SV Microwave, Inc.	
FINISH:	SEE NOTES	FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X'X' ±15'	1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	TITLE:	
SURFACE AREA:	N/A	DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005	INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	SMA PLUG TO JACK MICRO ATTENUATOR DC TO 18 GHz	
PROPRIETARY		THIRD ANGLE PROJECTION	DRAWN:	SEE SHEET 1	SIZE
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.			CHECKED:		DWG. NO.
			APPROVED:		M3933/25-XX
				SCALE: 4:1	SHEET 2 OF 2

Downloaded from Arrow.com