

REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
B	PROPOSAL DRAWING (EAR 14928)	FEB04/21	M.P.
C	PROPOSAL DRAWING (EAR 14932)	FEB05/21	M.P.

ORDERING CODE: **FLA - C X0 - 01**

**FLA SERIES**

**SHORTING OR OPEN CAP**




**CAP OPTIONS**

00 = OPEN CAP



10 = SHORTING CAP

20 = SHORTING CAP WITH MOV

**EXTENDED LIP FOR COVER  
& SILICONE RUBBER GASKET**



PRODUCT LABEL  
SCALE 4 : 1



**NOTES:**

- MATERIALS:
  - HOUSING: ENGINEERING THERMOPLASTIC, UL94V-0 FLAMMABILITY RATING
  - CONTACTS: COPPER ALLOY PLATED WITH MATTE TIN
  - SHORTING CLIP: COPPER ALLOY
  - O-RING & GASKET: SILICONE RUBBER, UL94V-0 FLAMMABILITY RATING
  - COVER: POLYCARBONATE, UL94-5VA FLAMMABILITY RATING
- DESIGNED IN ACCORDANCE WITH ANSI C136.10.
- INTENDED FOR USE WITH AMPHENOL'S ANSI C136.41 RECEPTACLES.
- IP66 PROTECTION AS PER IEC 60529.
- OUTDOOR RATING CERTIFIED TO UL773 REQUIREMENTS.



AMPHENOL P/N	DESCRIPTION	COVER COLOUR
FLA-C00-01	OPEN CAP	RED
FLA-C10-01	SHORTING CAP	BLACK
FLA-C20-01	SHORTING CAP WITH MOV	BLACK

UNLESS SPECIFIED OTHERWISE		DRAWN	M. PAHULJE	DEC08/20
PRIMARY UNITS	MILLIMETERS	CHECKED		
SECONDARY	INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES		Q.A. APP'D		
GENERAL TOLERANCES		DWG APPR.		
1 DECIMAL PLACE	±0.15	ENG. REL. NO.	EAR 14914	
2 DECIMAL PLACES		REF.		
3 DECIMAL PLACES		THIRD ANGLE PROJECTION		
ANGULAR DEGREES		DO NOT SCALE DRAWING		

**Amphenol Canada Corp.**  
Commercial Products  
FLA SHORTING & OPEN CAPS,  
COVER WITH EXTENDED LIP,  
WITH SILICONE RUBBER GASKET,  
RoHS COMPLIANT

DWG. NO. **P-FLA-CX0-01** REV **C**

CODE ID NO. **03554** DWG SIZE: **X** SCALE: **3:2** SHEET **1 OF 1**

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.