



RNF-3000-12/4-5-STK Product Details

Share

Print

Email



RNF-3000-12/4-5-STK

TE Internal Number: 4769982004

Active

Heat Shrink Tubing

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Heat Shrinkable Tubing
- Product Name = RNF-3000
- Product Source = U.K., U.S.
- Flexible
- Thin Wall Style

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Heat Shrinkable Tubing
- Color = Green

Dimensions:

- [Expanded ID, Min. \(mm \[in\]\)](#) = 12.00 [0.472]
- [Recovered ID, Max. \(mm \[in\]\)](#) = 4.00 [0.157]
- [Cut Length \(mm \[in\]\)](#) = 1220.00 [48.031]

Body Features:

- [Product Name](#) = RNF-3000
- Pliancy = Flexible
- [Wall Style](#) = Thin
- [Wall Type](#) = Single
- Material = Crosslinked Polyolefin
- [Shrink Ratio](#) = 3:1
- Fluid Type = Brake Fluid, Chemicals/Solvents, Water
- Resistant To = Abrasion, Fluids, Mechanical Damage, Strain
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 0.75 [0.0295]

Housing Features:

- Material Systems = No

Industry Standards:

- Government/Industry Qualification = No
- Flammability Rating Type = Flame-Retardant
- UL Rating = Recognized
- CSA Certified = Yes
- Approved Standards = BS 4G 198 Part 3 Type 11B, CSA LR31929, DEF Std 59-97 Type 2B, UL E35586, VDE 0341 Part 9005 Type A&B, VG95343 Part 5 Type A
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Fluid Resistance = Splash Protection
- [Operating Temperature \(°C\)](#) = -55 - +135

Conditions for Usage:

- Full Recovery Temperature (°C) = 120
- Shrink Temperature, Min. (°C) = 80
- High Temperature Compatible = No

Operation/Application:

- Application = Cable Jacket Repair Sleeve, Cable Jacketing, Color Coding, Identification, Insulation and Protection, Wire Bundling
- Emission Free = No
- Product Use = Cables, Electronic Components, Harnesses, Wire Terminations

Packaging Features:

- Packaging Method = Stick

Product Availability:

- Product Source = U.K., U.S.

Other:

- Brand = Raychem

Corporate Information

[About TE](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

[Terms & Conditions](#)

[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)

[Product Cross Reference](#)

[Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Knowledge Base](#)

[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

