



HOLE LAYOUT $\oplus 0.05$



CIRCUIT DIAGRAM
C: COMMON PIN
BOTTOM VIEW



Specifications:

Contact rating:	0.1A, 12V DC
Contact resistance:	20mOhm max.
Insulation resistance:	100MOhm min. at 500V DC for 1 minute
Dielectric strength:	500V AC (50/60Hz, 2mA) for 1 minute
Operating temperature:	-25°C to +85°C
Mechanical life:	10 000 cycles
Operating force:	250 +/-100gf
Soldering conditions:	260 +/-5°C, 5 +/-1sec.
Material:	Contact clip: phosphor bronze, silver plated Slider: PA66, black Spring plate: stainless steel, nickel plated Terminal: brass strip, silver plated Base: phenolic resin, natural Frame: steel, nickel plated

Compliance: RohS II (2011/65/EU)

Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm			Date	Name	MFP 213 N-RA	
			07/13	dr		
					30 28 93	
Slider material	01/15	dr	knitter-switch			Page
Modifications	Date	Name				1/1