NOTES:

I. MATERIAL AND FINISH:

BeCu, WHITE BRONZE PLATING BODIES: BeCu, GOLD PLATING OVER WHITE BRONZE CONTACT: SPRING RING: BeCu, GOLD PLATING OVER WHITE BRONZE

BeCu, WHITE BRONZE PLATING COVER:

FERRULE: SEAMLESS COPPER TUBING, WHITE BRONZE PLATING

INSULATOR :

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM

B. FREQUENCY RANGE: DC - 6 GHz

C. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.

3. MECHANICAL:

A. DURABILITY: 500 CYCLES MIN.

B. TEMPERATURE RANGE: -65° C TO 165° C

C. CRIMP WITH .105 INCH HEX.


4. PACKAGING:


A. QUANTITY: BULK PACK 100

B. MARKING: BAG TO BE MARKED


"AMPHENOL, 908-NM43200 100 PIECES, AND DATE CODE" AND "NON-MAGNETIC CONNECTORS"


5. ASTERISK (*) INDICATES CABLE ENTRY DIMENSIONS





RECOMMENDED CABLE STRIPPING DIMENSIONS





CUSTOMER OUTLINE DRAWING

0.5 - 6mm	6 - 30mm	30 - 120mm	ANGLES
±0.1mm	\pm 0.2mm	± 0.3mm	±ι°
NOTICE - These drawings,	specifications, or	other data (I) are,	and remain the
property of Amphenol corp			
confidential and not to k			
are given by Amphenol Cor			
other data by Amphenol Co			
not to be regarded by imp			
rights to permitting such			
product, process or design			ny way be related to
or disclosed by said draw	ııngs, specitication	s, or other data.	

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:

MATERIAL -	DRAWN R.CHEN	D A T E 28 - A u g - 12	
	ENGINEER K. CAPOZZI	DATE 18-Jul-06	
REFERENCE EAR # 1952 AND	APPROVED S.HSIEH	DATE 28 - Aug - 12	
CONFIGURATION LEVEL:	CAD FILE	_	
FINISH	1:\MMCX\908-NM4320	I:\MMCX\908-NM43200	

TITLE	
ASSEMBL	_Y MMCX
RG-178	R/A PLUG
NON MAC	SNETIC

SCALE: 12.0:1.0 SHEET 2 OF 2 DWG SIZE CODE ID REV

74868

Amphenol Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com

DRAWING NO. 908-NM43200 ITEM NO. 908-NM43200 PART NO. 908-NM43200