


EPIC® H-A 3 TGVV

Innovative metal and plastic housing design

The robust plastic cable coupler hood for rectangular connectors with a direct cable entry and one lever is ideal for use in control systems.

Info

Lightweight, chemically resistant plastic housing
Protection rating UL50E tested



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

Housing in plastic or metal version for safe connections in the smallest possible space

Application range

Machine and equipment manufacturing
Control engineering
Electronic laboratory

Product features

Cable coupler hood
1 lever
Straight cable entry

Last Update (05.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-A 3 TGVB

Versions with / without cable gland

Technical Data

| | |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material: | thermoplastic, grey, black Lever: zinc-plated steel |
| Protection rating: | IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched) |
| VDE-tested: | Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770 |
| Temperature range: | -40 °C to +100 °C, short-term up to +125 °C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-A 3 TGVB

| Article number | Article description | M | PG | Material | Colour | Cable gland | Cable clamping range | Pieces / PU |
|----------------|---------------------|----|----|---------------|--------|-------------|----------------------|-------------|
| 10429200 | H-A 3 Tgvb | - | 11 | Thermoplastic | black | - | - | 10 |
| 10429000 | H-A 3 Tgvb | - | 11 | Thermoplastic | grey | - | - | 10 |
| 10620300 | H-A 3 Tgvb | - | 11 | Thermoplastic | black | yes | 6.5 - 12 | 10 |
| 10429100 | H-A 3 Tgvb | - | 11 | Thermoplastic | grey | yes | 6.5 - 12 | 10 |
| 19429200 | H-A 3 Tgvb M20 | 20 | - | Thermoplastic | black | - | - | 10 |
| 19429000 | H-A 3 Tgvb M20 | 20 | - | Thermoplastic | grey | - | - | 10 |

Last Update (05.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

EPIC® H-A 3 TGVB

