

Vectron International**Filter specification****TFS 243E****1/5****Measurement condition**

Ambient temperature T_A :	23	°C
Input power level:	0	dBm
Terminating impedance: *		
Input:	350 Ω -3.8 pF	
Output:	350 Ω -3.8 pF	

Characteristics

Remark:

The reference level for the relative attenuation a_{rel} of the TFS 243E is the minimum of the pass band attenuation a_{min} . The minimum of the pass band attenuation a_{min} is defined as the insertion loss a_e . The centre frequency f_c is the arithmetic mean value of the upper and lower frequencies at the 3 dB filter attenuation level relative to the insertion loss a_e . The nominal frequency f_N is fixed at 243.0 MHz without any tolerance. The given values for both the relative attenuation a_{rel} and the group delay ripple have to be achieved at the frequencies given below even if the centre frequency f_c is shifted due to the temperature coefficient of frequency TC_f in the operating temperature range and due to a production tolerance for the centre frequency f_c .

D a t a	typ. value			tolerance / limit		
Insertion loss (reference level)	a_e	1.4	dB	max.	2.5	dB
Nominal frequency	f_N	-			243.0	MHz
Centre frequency at ambient temperature	f_c	243.0	MHz		242.9 ... 243.1	MHz
Passband	PB				$f_N \pm 25$	kHz
Pass band ripple		0.15	dB	max.	± 0.5	dB
Bandwidth	BW					
0.5 dB		-		min.	± 25	kHz
3 dB		440	kHz		-	
Relative attenuation	a_{rel}					
$f_N \pm 0.5$ MHz ... $f_N \pm 1.0$ MHz		15	dB	min.	7	dB
$f_N \pm 1.0$ MHz ... $f_N \pm 3.0$ MHz		30	dB	min.	25	dB
$f_N \pm 3.0$ MHz ... $f_N \pm 5.0$ MHz		37	dB	min.	25	dB
$f_N \pm 5.0$ MHz ... $f_N \pm 8.0$ MHz		43	dB	min.	25	dB
$f_N \pm 8.0$ MHz ... $f_N \pm 20.0$ MHz		48	dB	min.	40	dB
Input power level		-		max.	15	dBm
Operating temperature range	OTR	-			-40 ... +85	°C
Storage temperature range		-			-55 ... +125	°C
Frequency inversion temperature	T_o	+28	°C		-	
Temperature coefficient of frequency	TC_f^{**}	-0.032	ppm/K ²		-	

*) The terminating impedances depend on parasitics and q-values of matching elements and the board used, and are to be understood as reference values only. Should there be additional questions do not hesitate to ask for an application note or contact our design team.



**) $\Delta f = TC_f(T - T_o)^2 f_N$

Generated:**Checked / Approved:**

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com


Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

Filter characteristic




Construction and pin connection

(All dimensions in mm)



1	Input
2	Ground
3	Ground
4	Ground
5	Ground
6	Ground
7	Output
8	Ground
9	Ground
10	Ground
11	Ground
12	Ground

Date code: Year + week
 J 2017
 K 2018
 L 2019
 ...

50 Ω Test circuit

Vectron International GmbH
 Potsdamer Straße 18
 D 14 513 TELTOW / Germany
 Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
 E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information

Stability characteristics, reliability

After the following tests the filter shall meet the whole specification:

1. Shock: 500 g, 1 ms, half sine wave, 3 shocks each plane;
DIN IEC 60068 T2 - 27
2. Vibration: 10 Hz to 2000 Hz, 0.35 mm or 5 g respectively, 1 octave per min, 10 cycles per plane, 3 planes; DIN IEC 60068 T2 - 6
3. Change of temperature: -55 °C to 125 °C / 15 min. each / 100 cycles
DIN IEC 60068 part 2 – 14 Test N
4. Resistance to solder heat (reflow): reflow possible: three times max.;
for temperature conditions refer to the attached "Air reflow temperature conditions" on page 4;
5. SAW devices are Electrostatic Discharge (ESD) sensitive devices.

This filter is RoHS compliant (2011/65/EU)

Packing

Tape & Reel: IEC 286 – 3, with exception of value for N and minimum bending radius;
tape type II, embossed carrier tape with top cover tape on the upper side;


max. pieces of filters per reel:	3000
reel of empty components at start:	min. 300 mm
reel of empty components at start including leader:	min. 500 mm
trailer:	min. 300 mm

Tape (all dimensions in mm)

W	: 16.00 +0.3/-0.1
Po	: 4.00 ±0.1
Do	: 1.50 +0.1/-0
E	: 1.75 ±0.1
F	: 7.50 ±0.1
G(min)	: 0.75
P2	: 2.00 ±0.1
P1	: 8.00 ±0.1
D1(min)	: 1.50
Ao	: 5.40 ±0.1
Bo	: 7.60 ±0.1
Ct	: 13.30 ±0.1
Ko	: 2.00 ±0.1
t	: 0.30 ±0.05

Reel (all dimensions in mm)

A	: 330 or 180
W1	: 16.4 +2/-0
W2(max)	: 22.40
N(min)	: 50.00
C	: 13.0 +0.5/-0.2




The minimum bending radius is 45 mm.

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information

Air reflow temperature conditions

Conditions	Exposure
Average ramp-up rate (30 °C to 217 °C)	less than 3 °C / second
> 100 °C	between 300 and 600 seconds
> 150 °C	between 240 and 500 seconds
> 217 °C	between 30 and 150 seconds
Peak temperature	max. 260 °C
Time within 5 °C of actual peak temperature	between 10 and 30 seconds
Cool-down rate (Peak to 50 °C)	less than 6 °C / second
Time from 30 °C to Peak temperature	no greater than 300 seconds

Chip-mount air reflow profile

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information

Vectron International**Filter specification****TFS 243E****5/5****History**

Version	Reason of Changes	Name	Date
1.0	Generation of development specification.	Strehl	27.07.2005
1.1	Bandwidth @ 1 dB added.	Strehl	30.08.2005
1.2	Generation of filter specification and typical values added.	Sabah	27.10.2005
1.3	Insertion loss, bandwidth and relative attenuation updated. Stability characteristics updated.	Strehl	08.02.2006
1.4	Relative attenuation corrected.	Strehl	16.02.2006
1.5	Filter characteristic corrected.	Strehl	21.02.2006
2.0	Centre frequency at ambient temperature including tolerances added. Frequency inversion temperature added to data table.	Schönbein	03.02.2015
2.1	Storage temperature range updated.	Schönbein	11.05.2017

Vectron International GmbH
Potsdamer Straße 18
D 14 513 TELTOW / Germany
Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30
E-Mail: tft@vectron.com

Vectron International GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information