

SWITCH CIRCUIT		MATERIAL AND FINISH AS BELOW					
WHEN CARD IS EJECTED	WHEN CARD IS INSERTED	A	Housing	LCP UL94V-0, Color:Ivory	E		
		B	Contact	Brass C2680, Gold Plated Over Nickel	F		
		C	Holddown	Brass C2680, Tin Plated	G		
		D			H		





PIN NUMBER	DIM.L
25 26	3.50
ALL OTHER PINS	4.25
1 13 38 50	5.00

SPECIFICATION:

1. ELECTRICAL
1.1 Current Rating: 0.5AMP
1.2 Voltage Rating: 100VAC
1.3 Contact Resistance: 40mΩ
1.4 Insulation Resistance: 1000MΩ
1.5 Dielectric Withstanding Voltage: 500VAC for 1 minute

2. MECHANICAL
2.1 Durability: 10000Cycle
2.2 Insertion Force: 28.8N
2.3 Extraction Force: 4.9N

3. ENVIRONMENTAL
3.1 Operating temperature range: -40°C to +85°
3.2 Storage temperature range: -40°C to +85°

4. SOLDER ABILITY
4.1 Recommended IR Reflow Temperature: 260°C 10Sec

P1	P2	P3	P4	P5	P6	P7	P8	P9	P10	P11	P12

PIN ASSIGNMENT

PRODUCT NO.	DESCRIPTION
101D-TAAB-R01	CF Socket Slim Type Peg:38.74,Contact Area:Gold Flash

REV.	DESCRIPTION	DATE
3	Revise:	
2	Revise:	
1	Revise:	

UNLESS OTHERWISE SPECIFIED TOLERANCE

ANGLES	ANG.	±5°
LINEAR	0.	±0.3
	0.0	±0.25
	0.00	±0.20
SCALE	AS SHOWED	UNIT: mm
DRAWN	Willis	2012/11/13
CHECKED	Angel	2012/11/13
APPROVED	Ken	2012/11/13

ATTEND
www.attend.com.tw

DRAWN NAME: CF Slim Type Socket Locating Peg:38.74

PRODUCT NO.	101D-TAAB-R01
FILE NAME	101D-TAAB-R01_B_1

SIZE A4 REV. 1.0

Downloaded from Arrow.com.