


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - By Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.		

PART NUMBER	QTY	REMARKS
2155364-1	1	AC-5N-D
2155364-2	1	AC5ND PIN 63. With CE Ring. Repair part.
2155364-3	1	AC5ND PIN 64. With CE Ring. Repair part.
2155364-4	1	AC5ND PIN 65. With CE Ring. Repair part.



SPECIFICATIONS 仕様


Force at die face	公称出力	12.7kN	
Applicable wire range	圧着範囲	See options table	オプションの表を参照
Applicable terminal	適用端子	See options table	オプションの表を参照
Size	外形寸法	190x99x92mm Without foot pedal	フットペダル除く
Weight	質量	2.0kg Without foot pedal	フットペダル除く
Applicable air pressure	使用空気圧	0.5~0.6MPa (5~6kgf/cm ²)	
Air consumption	消費空気量	33 liters/min at 30 crimps/min	33L/min、使用回数30回/分の時
Operation	操作方法	Foot pedal	フットペダル
Joint of air hose	エアホース継手寸法	PT1/4	

ACCESSORIES 付属品

Foot pedal	フットペダル	AF-2
Air hose with joint	エアホース	2m, PT1/4

OPTIONS オプション別売り

Dies ダイス	No.1 head	1号ヘッド	1.25~5.5mm ²	Non-insulated	裸圧着端子、スリーブ		2155365-1
	No.3 head	3号ヘッド	1.25mm ²	Insulated	絶縁被覆付圧着端子、スリーブ		2155365-2
	No.4 head	4号ヘッド	2mm ²	Insulated	絶縁被覆付圧着端子、スリーブ		2155365-3
	No.5 head	5号ヘッド	5.5mm ²	Insulated	絶縁被覆付圧着端子、スリーブ		2155365-4
	No.7A head	7号Aヘッド	CE-2, CE-5	Closed end	絶縁被覆付閉端接続子		2155365-5
	No.8 head	8号ヘッド	CE-1, CE-8	Closed end	絶縁被覆付閉端接続子		2155365-6

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.NAKA 10SEP2011		 TE Connectivity						
		CHK S.NAKA 10SEP2011								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AC-5N-D PNEUMATIC CRIMPING TOOL						
		0 PLC ± -								
		1 PLC ± -								
		2 PLC ± -								
		3 PLC ± -								
		4 PLC ± -								
		ANGLES ± -								
MATERIAL -		FINISH -		APVD J.KOGA 10SEP2011		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
				PRODUCT SPEC -		A3		00779	C-2155364	-
				APPLICATION SPEC -						
				WEIGHT -						
CUSTOMER DRAWING						SCALE -		SHEET 1 of 1		REV A2