



XPT™ 650V GenX4™ IXXN110N65C4H1 w/ Sonic Diode

Extreme Light Punch Through
IGBT for 20-60kHz Switching



$$\begin{aligned} V_{CES} &= 650V \\ I_{C110} &= 110A \\ V_{CE(sat)} &\leq 2.35V \\ t_{fi(typ)} &= 35ns \end{aligned}$$

SOT-227B, miniBLOC
 E153432



G = Gate, C = Collector, E = Emitter
① either emitter terminal can be used as
Main or Kelvin Emitter

Symbol	Test Conditions	Maximum Ratings	
V_{CES}	$T_J = 25^\circ\text{C to } 175^\circ\text{C}$	650	V
V_{CGR}	$T_J = 25^\circ\text{C to } 175^\circ\text{C}, R_{GE} = 1M\Omega$	650	V
V_{GES}	Continuous	± 20	V
V_{GEM}	Transient	± 30	V
I_{C25}	$T_C = 25^\circ\text{C}$ (Chip Capability)	210	A
I_{C25}	Terminal Current Limit	200	A
I_{C110}	$T_C = 110^\circ\text{C}$	110	A
I_{F110}	$T_C = 110^\circ\text{C}$	70	A
I_{CM}	$T_C = 25^\circ\text{C}, 1\text{ms}$	670	A
SSOA (RBSOA)	$V_{GE} = 15V, T_{VJ} = 150^\circ\text{C}, R_G = 2\Omega$ Clamped Inductive Load	$I_{CM} = 220$ @ $V_{CE} \leq V_{CES}$	A
t_{sc} (SCSOA)	$V_{GE} = 15V, V_{CE} = 360V, T_J = 150^\circ\text{C}$ $R_G = 82\Omega$, Non Repetitive	10	μs
P_C	$T_C = 25^\circ\text{C}$	750	W
T_J		-55 ... +175	$^\circ\text{C}$
T_{JM}		175	$^\circ\text{C}$
T_{stg}		-55 ... +175	$^\circ\text{C}$
V_{ISOL}	50/60Hz $t = 1\text{min}$ $I_{ISOL} \leq 1\text{mA}$ $t = 1\text{s}$	2500 3000	V~ V~
M_d	Mounting Torque Terminal Connection Torque	1.5/13 1.3/11.5	Nm/lb.in Nm/lb.in
Weight		30	g

Features

- International Standard Package
- miniBLOC, with Aluminium Nitride Isolation
- 2500V~ Isolation Voltage
- Anti-Parallel Sonic Diode
- Optimized for 20-60kHz Switching
- Square RBSOA
- Short Circuit Capability
- High Current Handling Capability

Advantages

- High Power Density
- Low Gate Drive Requirement

Applications

- Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts
- High Frequency Power Inverters

Symbol	Test Conditions ($T_J = 25^\circ\text{C}$, Unless Otherwise Specified)	Characteristic Values		
		Min.	Typ.	Max.
BV_{CES}	$I_C = 250\mu\text{A}, V_{GE} = 0V$	650		V
$V_{GE(th)}$	$I_C = 4\text{mA}, V_{CE} = V_{GE}$	4.0		6.5 V
I_{CES}	$V_{CE} = V_{CES}, V_{GE} = 0V$ $T_J = 150^\circ\text{C}$			50 μA 3 mA
I_{GES}	$V_{CE} = 0V, V_{GE} = \pm 20V$			± 100 nA
$V_{CE(sat)}$	$I_C = 110A, V_{GE} = 15V$, Note 1 $T_J = 150^\circ\text{C}$	2.06 2.50		V V

Symbol Test Conditions


(T_J = 25°C Unless Otherwise Specified)

Characteristic Values

Min. Typ. Max.

g_{fs}	I _C = 60A, V _{CE} = 10V, Note 1	30	52	S
C_{ies}	V _{CE} = 25V, V _{GE} = 0V, f = 1MHz		5500	pF
C_{oes}			440	pF
C_{res}			80	pF
Q_{g(on)}	I _C = 110A, V _{GE} = 15V, V _{CE} = 0.5 • V _{CES}		167	nC
Q_{ge}			44	nC
Q_{gc}			63	nC
t_{d(on)}	Inductive load, T _J = 25°C I _C = 55A, V _{GE} = 15V V _{CE} = 400V, R _G = 2Ω Note 2		30	ns
t_{ri}			45	ns
E_{on}			2.50	mJ
t_{d(off)}			110	ns
t_{fi}			35	ns
E_{off}			0.63	mJ
t_{d(on)}	Inductive load, T _J = 150°C I _C = 55A, V _{GE} = 15V V _{CE} = 400V, R _G = 2Ω Note 2		26	ns
t_{ri}			45	ns
E_{on}			3.55	mJ
t_{d(off)}			120	ns
t_{fi}			40	ns
E_{off}			0.90	mJ
R_{thJC}				0.20 °C/W
R_{thCS}		0.05		°C/W

SOT-227B miniBLOC (IXXN)



SYM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	1.240	1.255	31.50	31.88
B	.307	.323	7.80	8.20
C	.161	.169	4.09	4.29
D	.161	.169	4.09	4.29
E	.161	.169	4.09	4.29
F	.587	.595	14.91	15.11
G	1.186	1.193	30.12	30.30
H	1.489	1.505	37.80	38.23
J	.460	.481	11.68	12.22
K	.351	.378	8.92	9.60
L	.030	.033	0.76	0.84
M	.496	.506	12.60	12.85
N	.990	1.001	25.15	25.42
O	.078	.084	1.98	2.13
P	.195	.235	4.95	5.97
Q	1.045	1.059	26.54	26.90
R	.155	.174	3.94	4.42
S	.186	.191	4.72	4.85
T	.968	.987	24.59	25.07
U	-.002	.004	-0.05	0.1
V	.130	.180	3.30	4.57
W	.780	.830	19.81	21.08

Reverse Sonic Diode (FRD)

Symbol Test Conditions

(T_J = 25°C Unless Otherwise Specified)

Characteristic Values

Min. Typ. Max.

V_F	I _F = 100A, V _{GE} = 0V, Note 1	T _J = 150°C	1.7	2.3	V
			1.8		V
I_{RM}	I _F = 100A, V _{GE} = 0V, -di _F /dt = 1500A/μs, V _R = 300V	T _J = 150°C	95		A
t_{rr}			100		ns
R_{thJC}				0.42	°C/W

Notes:

1. Pulse test, t ≤ 300μs, duty cycle, d ≤ 2%.
2. Switching times & energy losses may increase for higher V_{CE}(clamp), T_J or R_G.

IXYS Reserves the Right to Change Limits, Test Conditions, and Dimensions.

IXYS MOSFETs and IGBTs are covered 4,835,592 4,931,844 5,049,961 5,237,481 6,162,665 6,404,065 B1 6,683,344 6,727,585 7,005,734 B2 7,157,338B2
 by one or more of the following U.S. patents: 4,860,072 5,017,508 5,063,307 5,381,025 6,259,123 B1 6,534,343 6,710,405 B2 6,759,692 7,063,975 B2
 4,881,106 5,034,796 5,187,117 5,486,715 6,306,728 B1 6,583,505 6,710,463 6,771,478 B2 7,071,537







Fig. 1. Output Characteristics @ $T_J = 25^\circ\text{C}$

Fig. 2. Extended Output Characteristics @ $T_J = 25^\circ\text{C}$

Fig. 3. Output Characteristics @ $T_J = 150^\circ\text{C}$

Fig. 4. Dependence of $V_{CE(sat)}$ on Junction Temperature

Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage

Fig. 6. Input Admittance







Fig. 7. Transconductance

Fig. 8. Gate Charge

Fig. 9. Capacitance

Fig. 10. Reverse-Bias Safe Operating Area

Fig. 11. Maximum Transient thermal Impedance (IGBT)








Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance

Fig. 13. Inductive Switching Energy Loss vs. Collector Current

Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature

Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance

Fig. 16. Inductive Turn-off Switching Times vs. Collector Current

Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature


Fig. 18. Inductive Turn-on Switching Times vs. Gate Resistance




Fig. 19. Inductive Turn-on Switching Times vs. Collector Current




Fig. 20. Inductive Turn-on Switching Times vs. Junction Temperature




Fig. 21. Typ. Forward characteristics







Fig. 22. Typ. Reverse Recovery Charge Q_{rr} vs. $-di_F/dt$ Fig. 23. Typ. Peak Reverse Current I_{RM} vs. $-di_F/dt$ Fig. 24. Typ. Recovery Time t_{rr} vs. $-di_F/dt$ Fig. 25. Typ. Recovery Energy E_{rec} vs. $-di_F/dt$ 

Fig. 26. Maximum Transient Thermal Impedance (Diode)





Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.