





PRODUCT NUMBER	PITCH
YK222xx0x0J0G	6.35 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



MATERIALS & ELECTRICAL
 RATED VOLTAGE & CURRENT: cULus CQC 250 V, 10 A / 250 V, 9 A
 WITHSTAND VOLTAGE: AC 2000 V/Min
 INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANGE: -40 °C ~ +115 °C
 SCREW TORQUE VALUE: 5.3 Lb-In.
 WIRE RANGE: 22 - 18 AWG
 1) HOUSING: Thermoplastic, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL, M3

APPROVAL:

DIMENSION

Dim A	N×6.35±1.0
Dim B	(N-1)×6.35

N=Number of poles

Poles	Tolerance
2p-5p	±0.20
6p-10p	±0.25
11p-16p	±0.35
17p-24p	±0.40
25p-31p	±0.50

PART NO.: YK 222xx 0 x 0 J0G

No. of poles
 02 2 poles
 03 3 poles

 31 31 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK									
ltr	ecn no		dr	date		tolerances unless otherwise specified						title							
						angles		linear	X.±0.5		← MM →		TERMINAL BLOCK						
									X.X±0.3				BARRIER TYPE						
						X'±1"			X.XX±0.1				scale						
				dr	EVAN LU		061614			dwg no		sheet 1 of 1				size			
				engr	EVAN LU		061614			YK222xx0x0J0G						A4			
				chr	HANKE FENG		061614												
				appd	SHI JUN		061614					type		CUSTOMER Drawing					
sheet index		revision sheet		A 1															