


MIL-PRF-39006 Series



Military Conventional Wet Tantalum




This data sheet contains the MIL-PRF-39006 ratings for which AVX is a qualified approved supplier. This will be continually updated as the qualification expands. For COTS-Plus equivalent ratings please refer to the TWC data sheet located on the website.

This design is an axial leaded tubular case. It includes a welded tantalum can and header assembly that provides a hermetic seal to withstand harsh environments. The 1000 hour failure rates of 1%, 0.1% and 0.01% correspond to "M", "P", and "R" respectively. For details on testing conditions please refer to MIL-PRF-39006.

Currently qualified M39006 ratings include:

	M Level Reliability Dashes	P Level Reliability Dashes	R Level Reliability Dashes
M39006/22	-0001 to -0200	-0221 to -0420	-0441 to -0640
M39006/25	-0001 to -0080	-0121 to -0168	
M39006/30	-0001 to -0200	-0221 to -0420	-0441 to -0640
M39006/31	-0001 to -0080	-0121 to -0168	

OUTLINE DIMENSIONS



CASE DIMENSIONS: millimeters (inches)

DSCC Case Size	AVX Case Size	L +0.79 (0.031) -0.41 (0.016)	D Basic Case ± 0.41 (0.016)	D Insulated Case Max	E ± 6.35 (0.250)
T1	A	11.51 (0.453)	4.78 (0.188)	5.56 (0.219)	38.10 (1.500)
T2	B	16.28 (0.641)	7.14 (0.281)	7.92 (0.312)	57.15 (2.250)
T3	D	19.46 (0.766)	9.52 (0.375)	10.31 (0.406)	57.15 (2.250)
T4	E	26.97 (1.062)	9.52 (0.375)	10.31 (0.406)	57.15 (2.250)

VOLTAGE RATINGS (Operating Temperature -55°C to 125°C)

Voltage (DC)												
Rated Voltage: (V_r)	85°C	6	8	10	15	25	30	50	60	75	100	125
Derated Voltage: (V_d)	125°C	4	5	6	10	15	20	30	40	50	65	85
Surge Voltage: (V_s)	85°C	6.9	9.2	11.5	17.3	28.8	34.5	57.5	69	86.3	115	144




MIL-PRF-39006 Series

Military Conventional Wet Tantalum



HOW TO ORDER MILITARY M39006 PART NUMBER:



*High vibration qualified parts are currently under development. Please contact the factory for additional details and availability.

RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage^{1/ 2/ 3/}

Frequency of Applied Ripple Current		120Hz				800Hz				1kHz			
Ambient Still Air Temperature (°C)		≤55	85	105	125	≤55	85	105	125	≤55	85	105	125
% of	100%	0.60	0.39	—	—	0.71	0.43	—	—	0.72	0.45	—	—
85°C	90%	0.60	0.46	—	—	0.71	0.55	—	—	0.72	0.55	—	—
Rated	80%	0.60	0.52	0.35	—	0.71	0.62	0.42	—	0.72	0.62	0.42	—
Peak	70%	0.60	0.58	0.44	—	0.71	0.69	0.52	—	0.72	0.70	0.52	—
Voltage	66-2/3%	0.60	0.60	0.46	0.27	0.71	0.71	0.55	0.32	0.72	0.72	0.55	0.32

Frequency of Applied Ripple Current		10kHz				40kHz				100kHz			
Ambient Still Air Temperature (°C)		≤55	85	105	125	≤55	85	105	125	≤55	85	105	125
% of	100%	0.88	0.55	—	—	1.00	0.63	—	—	1.10	0.69	—	—
85°C	90%	0.88	0.67	—	—	1.00	0.77	—	—	1.10	0.85	—	—
Rated	80%	0.88	0.76	0.52	—	1.00	0.87	0.59	—	1.10	0.96	0.65	—
Peak	70%	0.88	0.85	0.64	—	1.00	0.97	0.73	—	1.10	1.07	0.80	—
Voltage	66-2/3%	0.88	0.88	0.68	0.40	1.00	1.00	0.77	0.45	1.10	1.10	0.85	0.50

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.

3/ The ripple current listed in the parametric tables represents a rating calculated by using a maximum internal temperature rise (ΔT) at 50°C at 40 kHz at 85°C ambient temperature, with a maximum peak rated voltage of 66.67 percent of the 85°C peak voltage rating.



MIL-PRF-39006 Series



Military Conventional Wet Tantalum

M39006 /22 RATINGS AND DASH NUMBER REFERENCE

M39006/22 Dashes			Tolerance ± (%)	Cap (µF) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	DC Leakage (µA)		DF max (%)	ESR max (Ohms) at 120Hz	Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size
M Level	P Level	R Level				+25°C	+85°C & 125°C				-55°C	+85°C	+125°C		
-0001	-0221	-0441	20	30	6	1	2	9	3.98	100	-40	10.5	12	820	T1
-0002	-0222	-0442	10												
-0003	-0223	-0443	5												
-0004	-0224	-0444	20	68	6	1	2	15	3.16	60	-40	14	16	960	T1
-0005	-0225	-0445	10												
-0006	-0226	-0446	5												
-0007	-0227	-0447	20	140	6	1	3	21	1.99	40	-40	14	16	1200	T2
-0008	-0228	-0448	10												
-0009	-0229	-0449	5												
-0010	-0230	-0450	20	270	6	1	6.5	45	2.21	25	-44	17.5	20	1375	T2
-0011	-0231	-0451	10												
-0012	-0232	-0452	5												
-0013	-0233	-0453	20	330	6	2	7.9	36	1.45	20	-44	14	16	1800	T3
-0014	-0234	-0454	10												
-0015	-0235	-0455	5												
-0016	-0236	-0456	20	560	6	2	13	55	1.3	25	-64	17.5	20	1900	T3
-0017	-0237	-0457	10												
-0018	-0238	-0458	5												
-0019	-0239	-0459	20	1200	6	3	14	90	1	20	-80	25	25	2265	T4
-0020	-0240	-0460	10												
-0021	-0241	-0461	20												
-0022	-0242	-0462	10	25	8	1	2	7.5	3.98	100	-40	10.5	12	820	T1
-0023	-0243	-0463	5												
-0024	-0244	-0464	20												
-0025	-0245	-0465	10	56	8	1	2	14	3.32	59	-40	14	16	900	T1
-0026	-0246	-0466	5												
-0027	-0247	-0467	20												
-0028	-0248	-0468	10	120	8	1	2	20	2.21	50	-44	17.5	20	1220	T2
-0029	-0249	-0469	5												
-0030	-0250	-0470	20												
-0031	-0251	-0471	10	220	8	1	7	37	2.23	30	-44	17.5	20	1370	T2
-0032	-0252	-0472	5												
-0033	-0253	-0473	20												
-0034	-0254	-0474	10	290	8	2	6	34	1.56	25	-64	17.5	20	1770	T3
-0035	-0255	-0475	5												
-0036	-0256	-0476	20												
-0037	-0257	-0477	10	430	8	2	14	46	1.42	25	-64	17.5	20	1825	T3
-0038	-0258	-0478	5												
-0039	-0259	-0479	20												
-0040	-0260	-0480	10	850	8	4	16	60	0.94	22	-80	25	25	2330	T4
-0041	-0261	-0481	20												
-0042	-0262	-0482	10												
-0043	-0263	-0483	5	20	10	1	2	6	3.98	175	-32	10.5	12	820	T1
-0044	-0264	-0484	20												
-0045	-0265	-0485	10												
-0046	-0266	-0486	5	47	10	1	2	13	3.67	100	-36	14	16	855	T1
-0047	-0267	-0487	20												
-0048	-0268	-0488	10												
-0049	-0269	-0489	5	100	10	1	4	15	1.99	60	-36	14	16	1200	T2
-0050	-0270	-0490	20												
-0051	-0271	-0491	10												
-0052	-0272	-0492	5	180	10	1	7	30	2.21	40	-36	14	16	1.365	T2
-0053	-0273	-0493	20												
-0054	-0274	-0494	10												
-0055	-0275	-0495	5	250	10	2	10	30	1.59	30	-40	14	16	1720	T3
-0056	-0276	-0496	20												
-0057	-0277	-0497	10												
-0058	-0278	-0498	5	390	10	2	16	44	1.5	25	-64	17.5	20	1800	T3
-0059	-0279	-0499	20												
-0060	-0280	-0500	10												
-0061	-0281	-0501	20	750	10	4	16	50	0.88	23	-80	25	25	2360	T4
-0062	-0282	-0502	10												
-0063	-0283	-0503	5												
-0064	-0284	-0504	20	15	15	1	2	5	4.42	155	-24	10.5	12	780	T1
-0065	-0285	-0505	10												
-0066	-0286	-0506	5												

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.



MIL-PRF-39006 Series



Military Conventional Wet Tantalum

M39006/22 Dashes			Tolerance ± (%)	Cap (µF) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	DC Leakage (µA)		DF max (%)	ESR max (Ohms) at 120Hz	Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size
M Level	P Level	R Level				+25°C	+85°C & 125°C				-55°C	+85°C	+125°C		
-0067	-0287	-0507	20	70	15	1	4	13	2.46	75	-28	14	16	1150	T2
-0068	-0288	-0508	10												
-0069	-0289	-0509	5												
-0070	-0290	-0510	20	120	15	1	7	18	1.99	50	-28	17.5	20	1450	T2
-0071	-0291	-0511	10												
-0072	-0292	-0512	5												
-0073	-0293	-0513	20	170	15	2	10	25	1.95	35	-32	14	16	1480	T3
-0074	-0294	-0514	10												
-0075	-0295	-0515	5												
-0076	-0296	-0516	20	270	15	2	16	32	1.57	30	-56	17.5	20	1740	T3
-0077	-0297	-0517	10												
-0078	-0298	-0518	5												
-0079	-0299	-0519	20	540	15	6	24	40	0.98	23	-80	25	25	2330	T4
-0080	-0300	-0520	10												
-0081	-0301	-0521	20												
-0082	-0302	-0522	10	10	25	1	2	4	5.31	220	-16	8	9	715	T1
-0083	-0303	-0523	5												
-0084	-0304	-0524	20												
-0085	-0305	-0525	10	22	25	1	2	6.6	3.98	140	-20	10.5	12	825	T1
-0086	-0306	-0526	5												
-0087	-0307	-0527	20												
-0088	-0308	-0528	10	50	25	1	2	11	2.92	70	-28	13	15	1130	T2
-0089	-0309	-0529	5												
-0090	-0310	-0530	20												
-0091	-0311	-0531	10	100	25	1	10	15	1.99	50	-28	13	15	1435	T2
-0092	-0312	-0532	5												
-0093	-0313	-0533	20												
-0094	-0314	-0534	10	120	25	2	6	21	2.32	38	-32	13	15	1450	T3
-0095	-0315	-0535	5												
-0096	-0316	-0536	20												
-0097	-0317	-0537	10	180	25	2	18	26	1.92	32	-48	13	15	1525	T3
-0098	-0318	-0538	5												
-0099	-0319	-0539	20												
-0100	-0320	-0540	10	350	25	7	28	35	1.33	24	-70	25	25	1970	T4
-0101	-0321	-0541	20												
-0102	-0322	-0542	10												
-0103	-0323	-0543	5	8	30	1	2	4	6.64	275	-16	8	12	640	T1
-0104	-0324	-0544	20												
-0105	-0325	-0545	10												
-0106	-0326	-0546	5	15	30	1	2	5	4.42	175	-20	10.5	12	780	T1
-0107	-0327	-0547	20												
-0108	-0328	-0548	10												
-0109	-0329	-0549	5	40	30	1	5	10	3.32	65	-24	10.5	12	1120	T2
-0110	-0330	-0550	20												
-0111	-0331	-0551	10												
-0112	-0332	-0552	5	68	30	1	8	13	2.54	60	-24	13	15	1285	T2
-0113	-0333	-0553	20												
-0114	-0334	-0554	10												
-0115	-0335	-0555	5	100	30	2	12	17	2.26	40	-28	10.5	12	1450	T3
-0116	-0336	-0556	20												
-0117	-0337	-0557	10												
-0118	-0338	-0558	5	150	30	2	18	23	2.03	35	-48	13	15	1525	T3
-0119	-0339	-0559	20												
-0120	-0340	-0560	10												
-0121	-0341	-0561	20	300	30	8	32	31	1.37	25	-60	25	25	1950	T4
-0122	-0342	-0562	10												
-0123	-0343	-0563	5												
-0124	-0344	-0564	20	10	50	1	2	4	5.31	250	-24	8	9	715	T1
-0125	-0345	-0565	10												
-0126	-0346	-0566	5												
-0127	-0347	-0567	20	25	50	1	5	8	4.25	95	-20	10.5	12	1005	T2
-0128	-0348	-0568	10												
-0129	-0349	-0569	5												
-0130	-0350	-0570	20	47	50	1	9	11	3.11	70	-28	13	15	1155	T2
-0131	-0351	-0571	10												
-0132	-0352	-0572	5												
-0133	-0353	-0573	20	60	50	2	12	12	2.65	45	-16	10.5	12	1335	T3
-0134	-0354	-0574	10												
-0135	-0355	-0575	5												

MIL-PRF-39006 Series



Military Conventional Wet Tantalum

M39006/22 Dashes			Tolerance ± (%)	Cap (µF) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	DC Leakage (µA)		DF max (%)	ESR max (Ohms) at 120Hz	Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size
M Level	P Level	R Level				+25°C	+85°C & 125°C				-55°C	+85°C	+125°C		
-0136	-0356	-0576	20	82	50	2	16	15	2.43	45	-32	13	15	1400	T3
-0137	-0357	-0577	10												
-0138	-0358	-0578	5												
-0139	-0359	-0579	20	160	50	8	32	17	1.41	27	-50	25	25	1900	T4
-0140	-0360	-0580	10												
-0141	-0361	-0581	20												
-0142	-0362	-0582	10	4	60	1	2	2.8	9.29	550	-16	5	6	525	T1
-0143	-0363	-0583	5												
-0144	-0364	-0584	20												
-0145	-0365	-0585	10	8.2	60	1	2	4	6.47	275	-24	8	9	625	T1
-0146	-0366	-0586	5												
-0147	-0367	-0587	20												
-0148	-0368	-0588	10	20	60	1	5	7	4.64	105	-16	10.5	12	930	T2
-0149	-0369	-0589	5												
-0150	-0370	-0590	20												
-0151	-0371	-0591	10	39	60	1	9	10	3.4	90	-28	10.5	12	1110	T2
-0152	-0372	-0592	5												
-0153	-0373	-0593	20												
-0154	-0374	-0594	10	50	60	2	12	10	2.65	50	-16	10.5	12	1330	T3
-0155	-0375	-0595	5												
-0156	-0376	-0596	20												
-0157	-0377	-0597	10	68	60	2	16	13	2.54	50	-32	10.5	12	1365	T3
-0158	-0378	-0598	5												
-0159	-0379	-0599	20												
-0160	-0380	-0600	10	140	60	8	32	16	1.52	28	-40	20	20	1850	T4
-0161	-0381	-0601	20												
-0162	-0382	-0602	10												
-0163	-0383	-0603	5	3.5	75	1	2	2.5	9.48	650	-16	5	6	525	T1
-0164	-0384	-0604	20												
-0165	-0385	-0605	10												
-0166	-0386	-0606	5	6.8	75	1	2	3.5	6.83	300	-20	8	9	610	T1
-0167	-0387	-0607	20												
-0168	-0388	-0608	10												
-0169	-0389	-0609	5	15	75	1	5	6	5.31	150	-16	8	9	890	T2
-0170	-0390	-0610	20												
-0171	-0391	-0611	10												
-0172	-0392	-0612	5	33	75	1	10	10	4.02	90	-24	10.5	15	1000	T2
-0173	-0393	-0613	20												
-0174	-0394	-0614	10												
-0175	-0395	-0615	5	40	75	2	12	9	2.99	60	-16	10.5	12	1250	T3
-0176	-0396	-0616	20												
-0177	-0397	-0617	10												
-0178	-0398	-0618	5	56	75	2	17	11	2.61	60	-28	10.5	15	1335	T3
-0179	-0399	-0619	20												
-0180	-0400	-0620	10												
-0181	-0401	-0621	20	110	75	9	36	12	1.45	29	-35	20	20	1850	T4
-0182	-0402	-0622	10												
-0183	-0403	-0623	5												
-0184	-0404	-0624	20	2.5	100	1	2	2	10.62	950	-16	7	8	505	T1
-0185	-0405	-0625	10												
-0186	-0406	-0626	5												
-0187	-0407	-0627	20	4.7	100	1	2	3	8.47	500	-16	7	8	565	T1
-0188	-0408	-0628	10												
-0189	-0409	-0629	5												
-0190	-0410	-0630	20	11	100	1	4	5	6.03	200	-16	8	8	835	T2
-0191	-0411	-0631	10												
-0192	-0412	-0632	5												
-0193	-0413	-0633	20	22	100	1	9	7.5	4.52	100	-16	8	8	965	T2
-0194	-0414	-0634	10												
-0195	-0415	-0635	5												
-0196	-0416	-0636	20	30	100	2	12	7	3.1	80	-16	8	8	1240	T3
-0197	-0417	-0637	10												
-0198	-0418	-0638	5												
-0199	-0419	-0639	20	43	100	2	17	8.5	2.62	70	-20	8	8	1335	T3
-0200	-0420	-0640	10												
-0200	-0420	-0640	10												

MIL-PRF-39006 Series



Military Conventional Wet Tantalum

M39006/25 RATINGS AND DASH NUMBER REFERENCE

M39006/25 Dashes		Tolerance ± (%)	Cap (µF) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	DC Leakage (µA)		DF max (%)	ESR max (Ohms) at 120Hz	Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size
M Level	P Level				+25°C	+85°C & 125°C				-55°C	+85°C	+125°C		
-0001	-	20	220	6	2	9	50	3.02	36	-64	13	16	1000	T1
-0002	-	10												
-0003	-	20	820	6	3	14	155	2.51	18	-88	16	20	1500	T2
-0004	-	10												
-0005	-	20	1500	6	5	20	172	1.52	18	-90	20	25	1900	T3
-0006	-	10												
-0007	-	20	2200	6	6	24	170	1.03	13	-90	25	30	2300	T4
-0008	-	10												
-0009	-	20	180	8	2	9	41	3.02	45	-60	13	16	1000	T1
-0010	-	10												
-0011	-	20	680	8	3	14	130	2.54	22	-83	16	20	1500	T2
-0012	-	10												
-0013	-	20	1500	8	5	20	170	1.5	18	-90	20	25	1900	T3
-0014	-	10												
-0015	-	20	1800	8	7	25	138	1.02	14	-90	25	30	2300	T4
-0016	-	10												
-0017	-	20	150	10	2	9	34	3.01	54	-55	13	16	900	T1
-0018	-	10												
-0019	-	20	560	10	3	16	106	2.51	27	-77	16	20	1450	T2
-0020	-	10												
-0021	-	20	1200	10	5	20	137	1.51	18	-88	20	25	1850	T3
-0022	-	10												
-0023	-	20	1500	10	7	25	114	1.01	15	-88	25	30	2300	T4
-0024	-	10												
-0025	-	20	100	15	2	9	30	3.98	72	-44	13	16	900	T1
-0026	-	10												
-0027	-	20	390	15	3	16	74	2.52	31	-66	16	20	1450	T2
-0028	-	10												
-0029	-	20	820	15	6	24	111	1.8	22	-77	20	25	1800	T3
-0030	-	10												
-0031	-	20	1000	15	8	32	92	1.22	17	-77	25	30	2300	T4
-0032	-	10												
-0033	-0121	20	68	25	2	9	22	4.29	90	-40	12	15	850	T1
-0034	-0122	10												
-0035	-0123	20	270	25	3	16	55	2.7	33	-62	13	16	1400	T2
-0036	-0124	10												
-0037	-0125	20	560	25	7	28	76	1.8	24	-72	20	25	1750	T3
-0038	-0126	10												
-0039	-0127	20	680	25	8	32	63	1.23	19	-72	25	30	2100	T4
-0040	-0128	10												
-0041	-0129	20	56	30	2	9	22	5.21	100	-38	12	15	800	T1
-0042	-0130	10												
-0043	-0131	20	220	30	3	16	42	2.53	36	-60	13	16	1200	T2
-0044	-0132	10												
-0045	-0133	20	470	30	8	32	64	1.81	25	-65	20	25	1500	T3
-0046	-0134	10												
-0047	-0135	20	560	30	9	36	55	1.3	20	-65	25	30	2000	T4
-0048	-0136	10												
-0049	-0137	20	33	50	2	9	12.3	4.95	135	-29	10	12	700	T1
-0050	-0138	10												
-0051	-0139	20	120	50	4	24	22.5	2.49	49	-42	12	15	1200	T2
-0052	-0140	10												
-0053	-0141	20	270	50	8	32	37	1.82	29	-46	20	25	1450	T3
-0054	-0142	10												
-0055	-0143	20	330	50	9	36	38	1.53	22	-46	25	30	1900	T4
-0056	-0144	10												
-0057	-0145	20	27	60	3	12	10.2	5.01	144	-24	10	12	700	T1
-0058	-0146	10												
-0059	-0147	20	100	60	4	20	19	2.52	54	-36	12	15	1100	T2
-0060	-0148	10												
-0061	-0149	20	220	60	8	32	30	1.81	29	-40	16	20	1400	T3
-0062	-0150	10												
-0063	-0151	20	270	60	9	36	27	1.33	23	-45	20	25	1850	T4
-0064	-0152	10												
-0065	-0153	20	22	75	3	12	8.5	5.13	157	-19	10	12	600	T1
-0066	-0154	10												

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.



MIL-PRF-39006 Series



Military Conventional Wet Tantalum

M39006/25 RATINGS AND DASH NUMBER REFERENCE

M39006/25 Dashes		Tolerance ± (%)	Cap (µF) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	DC Leakage (µA)		DF max (%)	ESR max (Ohms) at 120Hz	Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size
M Level	P Level				+25°C	+85°C & 125°C				-55°C	+85°C	+125°C		
-0067	-0155	20	82	75	4	24	15.2	2.46	63	-30	12	15	1000	T2
-0068	-0156	10												
-0069	-0157	20	180	75	9	36	24.4	2.23	30	-35	16	20	1300	T3
-0070	-0158	10												
-0071	-0159	20	220	75	10	40	37	1.8	24	-40	20	25	1800	T4
-0072	-0160	10												
-0073	-0161	20	10	100	3	12	4.5	5.97	200	-17	10	12	800	T1
-0074	-0162	10												
-0075	-0163	20	39	100	5	24	10.4	3.54	80	-20	12	15	1300	T2
-0076	-0164	10												
-0077	-0165	20	68	100	10	40	11.3	2.21	40	-30	14	16	1600	T3
-0078	-0166	10												
-0079	-0167	20	120	100	12	48	25	2.76	30	-35	15	17	2000	T4
-0080	-0168	10												

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V.
DCL is measured at rated voltage after 5 minutes.



MIL-PRF-39006 Series



Military Conventional Wet Tantalum

M39006 /30 RATINGS AND DASH NUMBER REFERENCE

M39006/30 Dashes			Tolerance ± (%)	Cap (µF) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	DC Leakage (µA)		DF max (%)	ESR max (Ohms) at 120Hz	Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size
M Level	P Level	R Level				+25°C	+85°C & 125°C				-55°C	+85°C	+125°C		
-0001	-0221	-0441	20	30	6	1	2	4.5	1.99	100	-40	10.5	12	820	T1
-0002	-0222	-0442	10												
-0003	-0223	-0443	5												
-0004	-0224	-0444	20	68	6	1	2	7.5	1.58	60	-40	14	16	960	T1
-0005	-0225	-0445	10												
-0006	-0226	-0446	5												
-0007	-0227	-0447	20	140	6	1	3	10.5	0.99	40	-40	14	16	1200	T2
-0008	-0228	-0448	10												
-0009	-0229	-0449	5												
-0010	-0230	-0450	20	270	6	1	6.5	22.5	1.11	25	-44	17.5	20	1375	T2
-0011	-0231	-0451	10												
-0012	-0232	-0452	5												
-0013	-0233	-0453	20	330	6	2	7.9	18	0.73	20	-44	14	16	1800	T3
-0014	-0234	-0454	10												
-0015	-0235	-0455	5												
-0016	-0236	-0456	20	560	6	2	13	27.5	0.65	25	-64	17.5	20	1900	T3
-0017	-0237	-0457	10												
-0018	-0238	-0458	5												
-0019	-0239	-0459	20	1200	6	3	14	45	0.5	20	-80	25	25	2265	T4
-0020	-0240	-0460	10												
-0021	-0241	-0461	20												
-0022	-0242	-0462	10	25	8	1	2	3.75	1.99	100	-40	10.5	12	820	T1
-0023	-0243	-0463	5												
-0024	-0244	-0464	20												
-0025	-0245	-0465	10	56	8	1	2	7	1.66	59	-40	14	16	900	T1
-0026	-0246	-0466	5												
-0027	-0247	-0467	20												
-0028	-0248	-0468	10	120	8	1	2	10	1.11	50	-44	17.5	20	1220	T2
-0029	-0249	-0469	5												
-0030	-0250	-0470	20												
-0031	-0251	-0471	10	220	8	1	7	18.5	1.12	30	-44	17.5	20	1370	T2
-0032	-0252	-0472	5												
-0033	-0253	-0473	20												
-0034	-0254	-0474	10	290	8	2	6	17	0.78	25	-64	17.5	20	1770	T3
-0035	-0255	-0475	5												
-0036	-0256	-0476	20												
-0037	-0257	-0477	10	430	8	2	14	23	0.71	25	-64	17.5	20	1825	T3
-0038	-0258	-0478	5												
-0039	-0259	-0479	20												
-0040	-0260	-0480	10	850	8	4	16	30	0.47	22	-80	25	25	2330	T4
-0041	-0261	-0481	20												
-0042	-0262	-0482	10												
-0043	-0263	-0483	5	20	10	1	2	3	1.99	175	-32	10.5	12	820	T1
-0044	-0264	-0484	20												
-0045	-0265	-0485	10												
-0046	-0266	-0486	5	47	10	1	2	6.5	1.84	100	-36	14	16	855	T1
-0047	-0267	-0487	20												
-0048	-0268	-0488	10												
-0049	-0269	-0489	5	100	10	1	4	7.5	0.99	60	-36	14	16	1200	T2
-0050	-0270	-0490	20												
-0051	-0271	-0491	10												
-0052	-0272	-0492	5	180	10	1	7	15	1.11	40	-36	14	16	1,365	T2
-0053	-0273	-0493	20												
-0054	-0274	-0494	10												
-0055	-0275	-0495	5	250	10	2	10	15	0.8	30	-40	14	16	1720	T3
-0056	-0276	-0496	20												
-0057	-0277	-0497	10												
-0058	-0278	-0498	5	390	10	2	16	22	0.75	25	-64	17.5	20	1800	T3
-0059	-0279	-0499	20												
-0060	-0280	-0500	10												
-0061	-0281	-0501	20	750	10	4	16	25	0.44	23	-80	25	25	2360	T4
-0062	-0282	-0502	10												
-0063	-0283	-0503	5												
-0064	-0284	-0504	20	15	15	1	2	2.5	2.21	155	-24	10.5	12	780	T1
-0065	-0285	-0505	10												
-0066	-0286	-0506	5												

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V.
DCL is measured at rated voltage after 5 minutes.



MIL-PRF-39006 Series



Military Conventional Wet Tantalum

M39006/30 Dashes			Tolerance ± (%)	Cap (µF) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	DC Leakage (µA)		DF max (%)	ESR max (Ohms) at 120Hz	Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size
M Level	P Level	R Level				+25°C	+85°C & 125°C				-55°C	+85°C	+125°C		
-0067	-0287	-0507	20	70	15	1	4	6.5	1.23	75	-28	14	16	1150	T2
-0068	-0288	-0508	10												
-0069	-0289	-0509	5												
-0070	-0290	-0510	20	120	15	1	7	9	0.99	50	-28	17.5	20	1450	T2
-0071	-0291	-0511	10												
-0072	-0292	-0512	5												
-0073	-0293	-0513	20	170	15	2	10	12.5	0.98	35	-32	14	16	1480	T3
-0074	-0294	-0514	10												
-0075	-0295	-0515	5												
-0076	-0296	-0516	20	270	15	2	16	16	0.79	30	-56	17.5	20	1740	T3
-0077	-0297	-0517	10												
-0078	-0298	-0518	5												
-0079	-0299	-0519	20	540	15	6	24	20	0.49	23	-80	25	25	2330	T4
-0080	-0300	-0520	10												
-0081	-0301	-0521	20												
-0082	-0302	-0522	10	10	25	1	2	2	2.66	220	-16	8	9	715	T1
-0083	-0303	-0523	5												
-0084	-0304	-0524	20												
-0085	-0305	-0525	10	22	25	1	2	3.3	1.99	140	-20	10.5	12	825	T1
-0086	-0306	-0526	5												
-0087	-0307	-0527	20												
-0088	-0308	-0528	10	50	25	1	2	5.5	1.46	70	-28	13	15	1130	T2
-0089	-0309	-0529	5												
-0090	-0310	-0530	20												
-0091	-0311	-0531	10	100	25	1	10	7.5	0.99	50	-28	13	15	1435	T2
-0092	-0312	-0532	5												
-0093	-0313	-0533	20												
-0094	-0314	-0534	10	120	25	2	6	10.5	1.16	38	-32	13	15	1450	T3
-0095	-0315	-0535	5												
-0096	-0316	-0536	20												
-0097	-0317	-0537	10	180	25	2	18	13	0.96	32	-48	13	15	1525	T3
-0098	-0318	-0538	5												
-0099	-0319	-0539	20												
-0100	-0320	-0540	10	350	25	7	28	17.5	0.67	24	-70	25	25	1970	T4
-0101	-0321	-0541	20												
-0102	-0322	-0542	10												
-0103	-0323	-0543	5	8	30	1	2	2	3.32	275	-16	8	12	640	T1
-0104	-0324	-0544	20												
-0105	-0325	-0545	10												
-0106	-0326	-0546	5	15	30	1	2	2.5	2.21	175	-20	10.5	12	780	T1
-0107	-0327	-0547	20												
-0108	-0328	-0548	10												
-0109	-0329	-0549	5	40	30	1	5	5	1.66	65	-24	10.5	12	1120	T2
-0110	-0330	-0550	20												
-0111	-0331	-0551	10												
-0112	-0332	-0552	5	68	30	1	8	6.5	1.27	60	-24	13	15	1285	T2
-0113	-0333	-0553	20												
-0114	-0334	-0554	10												
-0115	-0335	-0555	5	100	30	2	12	8.5	1.13	40	-28	10.5	12	1450	T3
-0116	-0336	-0556	20												
-0117	-0337	-0557	10												
-0118	-0338	-0558	5	150	30	2	18	11.5	1.02	35	-48	13	15	1525	T3
-0119	-0339	-0559	20												
-0120	-0340	-0560	10												
-0121	-0341	-0561	20	300	30	8	32	15.5	0.69	25	-60	25	25	1950	T4
-0122	-0342	-0562	10												
-0123	-0343	-0563	5												
-0124	-0344	-0564	20	5	50	1	2	1.5	3.98	400	-16	5	6	580	T1
-0125	-0345	-0565	10												
-0126	-0346	-0566	5												
-0127	-0347	-0567	20	10	50	1	2	2	2.66	250	-24	8	9	715	T1
-0128	-0348	-0568	10												
-0129	-0349	-0569	5												
-0130	-0350	-0570	20	25	50	1	5	4	2.13	95	-20	10.5	12	1005	T2
-0131	-0351	-0571	10												
-0132	-0352	-0572	5												

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

MIL-PRF-39006 Series



Military Conventional Wet Tantalum

M39006/30 Dashes			Tolerance ± (%)	Cap (µF) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	DC Leakage (µA)		DF max (%)	ESR max (Ohms) at 120Hz	Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size
M Level	P Level	R Level				+25°C	+85°C & 125°C				-55°C	+85°C	+125°C		
-0133	-0353	-0573	20	60	50	2	12	6	1.33	45	-16	10.5	12	1335	T3
-0134	-0354	-0574	10												
-0135	-0355	-0575	5												
-0136	-0356	-0576	20												
-0137	-0357	-0577	10	82	50	2	16	7.5	1.22	45	-32	13	15	1400	T3
-0138	-0358	-0578	5												
-0139	-0359	-0579	20												
-0140	-0360	-0580	10												
-0141	-0361	-0581	20	4	60	1	2	1.4	4.65	550	-16	5	6	525	T1
-0142	-0362	-0582	10												
-0143	-0363	-0583	5												
-0144	-0364	-0584	20												
-0145	-0365	-0585	10	8.2	60	1	2	2	3.24	275	-24	8	9	625	T1
-0146	-0366	-0586	5												
-0147	-0367	-0587	20												
-0148	-0368	-0588	10												
-0149	-0369	-0589	5	20	60	1	5	3.5	2.32	105	-16	10.5	12	930	T2
-0150	-0370	-0590	20												
-0151	-0371	-0591	10												
-0152	-0372	-0592	5												
-0153	-0373	-0593	20	39	60	1	9	5	1.7	90	-28	10.5	12	1110	T2
-0154	-0374	-0594	10												
-0155	-0375	-0595	5												
-0156	-0376	-0596	20												
-0157	-0377	-0597	10	68	60	2	16	6.5	1.27	50	-32	10.5	12	1365	T3
-0158	-0378	-0598	5												
-0159	-0379	-0599	20												
-0160	-0380	-0600	10												
-0161	-0381	-0601	20	3.5	75	1	2	1.25	4.74	650	-16	5	6	525	T1
-0162	-0382	-0602	10												
-0163	-0383	-0603	5												
-0164	-0384	-0604	20												
-0165	-0385	-0605	10	6.8	75	1	2	1.75	3.42	300	-20	8	9	610	T1
-0166	-0386	-0606	5												
-0167	-0387	-0607	20												
-0168	-0388	-0608	10												
-0169	-0389	-0609	5	15	75	1	5	3	2.66	150	-16	8	9	890	T2
-0170	-0390	-0610	20												
-0171	-0391	-0611	10												
-0172	-0392	-0612	5												
-0173	-0393	-0613	20	40	75	2	12	4.5	1.5	60	-16	10.5	12	1250	T3
-0174	-0394	-0614	10												
-0175	-0395	-0615	5												
-0176	-0396	-0616	20												
-0177	-0397	-0617	10	56	75	2	17	5.5	1.31	60	-28	10.5	15	1335	T3
-0178	-0398	-0618	5												
-0179	-0399	-0619	20												
-0180	-0400	-0620	10												
-0181	-0401	-0621	20	2.5	100	1	2	1	5.31	950	-16	7	8	505	T1
-0182	-0402	-0622	10												
-0183	-0403	-0623	5												
-0184	-0404	-0624	20												
-0185	-0405	-0625	10	4.7	100	1	2	1.5	4.24	500	-16	7	8	565	T1
-0186	-0406	-0626	5												
-0187	-0407	-0627	20												
-0188	-0408	-0628	10												
-0189	-0409	-0629	5	11	100	1	4	2.5	3.02	200	-16	8	8	835	T2
-0190	-0410	-0630	20												
-0191	-0411	-0631	10												
-0192	-0412	-0632	5												
-0193	-0413	-0633	20	30	100	2	12	3.5	1.55	80	-16	8	8	1240	T3
-0194	-0414	-0634	10												
-0195	-0415	-0635	5												
-0196	-0416	-0636	20												
-0197	-0417	-0637	10	43	100	2	17	4.25	1.31	70	-20	8	8	1335	T3
-0198	-0418	-0638	5												
-0199	-0419	-0639	20												
-0200	-0420	-0640	10												

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V.
DCL is measured at rated voltage after 5 minutes.



MIL-PRF-39006 Series



Military Conventional Wet Tantalum

M39006 /31 RATINGS AND DASH NUMBER REFERENCE

M39006/31 Dashes		Tolerance ± (%)	Cap (µF) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	DC Leakage (µA)		DF max (%)	ESR max (Ohms) at 120Hz	Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size
M Level	P Level				+25°C	+85°C & 125°C				-55°C	+85°C	+125°C		
-0001	-	20	220	6	2	9	25	1.51	36	-64	13	16	1000	T1
-0002	-	10												
-0003	-	20	820	6	3	14	77.5	1.26	18	-88	16	20	1500	T2
-0004	-	10												
-0005	-	20	1500	6	5	20	86	0.76	18	-90	20	25	1900	T3
-0006	-	10												
-0007	-	20	2200	6	6	24	85	0.52	13	-90	25	30	2300	T4
-0008	-	10												
-0009	-	20	180	8	2	9	20.5	1.51	45	-60	13	16	1000	T1
-0010	-	10												
-0011	-	20	680	8	3	14	65	1.27	22	-83	16	20	1500	T2
-0012	-	10												
-0013	-	20	1500	8	5	20	85	0.75	18	-90	20	25	1900	T3
-0014	-	10												
-0015	-	20	1800	8	7	25	69	0.51	14	-90	25	30	2300	T4
-0016	-	10												
-0017	-	20	150	10	2	9	17	1.51	54	-55	13	16	900	T1
-0018	-	10												
-0019	-	20	560	10	3	16	53	1.26	27	-77	16	20	1450	T2
-0020	-	10												
-0021	-	20	1200	10	5	20	68.5	0.76	18	-88	20	25	1850	T3
-0022	-	10												
-0023	-	20	1500	10	7	25	57	0.51	15	-88	25	30	2300	T4
-0024	-	10												
-0025	-	20	100	15	2	9	15	1.99	72	-44	13	16	900	T1
-0026	-	10												
-0027	-	20	390	15	3	16	37	1.26	31	-66	16	20	1450	T2
-0028	-	10												
-0029	-	20	820	15	6	24	55.5	0.9	22	-77	20	25	1800	T3
-0030	-	10												
-0031	-	20	1000	15	8	32	46	0.61	17	-77	25	30	2300	T4
-0032	-	10												
-0033	-0121	20	68	25	2	9	11	2.15	90	-40	12	15	850	T1
-0034	-0122	10												
-0035	-0123	20	270	25	3	16	27.5	1.35	33	-62	13	16	1400	T2
-0036	-0124	10												
-0037	-0125	20	560	25	7	28	38	0.9	24	-72	20	25	1750	T3
-0038	-0126	10												
-0039	-0127	20	680	25	8	32	31.5	0.62	19	-72	25	30	2100	T4
-0040	-0128	10												
-0041	-0129	20	56	30	2	9	11	2.61	100	-38	12	15	800	T1
-0042	-0130	10												
-0043	-0131	20	220	30	3	16	21	1.27	36	-60	13	16	1200	T2
-0044	-0132	10												
-0045	-0133	20	470	30	8	32	32	0.91	25	-65	20	25	1500	T3
-0046	-0134	10												
-0047	-0135	20	560	30	9	36	27.5	0.65	20	-65	25	30	2000	T4
-0048	-0136	10												
-0049	-0137	20	33	50	2	9	6.15	2.48	135	-29	10	12	700	T1
-0050	-0138	10												
-0051	-0139	20	120	50	4	24	11.3	1.25	49	-42	12	15	1200	T2
-0052	-0140	10												
-0053	-0141	20	270	50	8	32	18.5	0.91	29	-46	20	25	1450	T3
-0054	-0142	10												
-0055	-0143	20	330	50	9	36	19	0.77	22	-46	25	30	1900	T4
-0056	-0144	10												
-0057	-0145	20	27	60	3	12	5.1	2.51	144	-24	10	12	700	T1
-0058	-0146	10												
-0059	-0147	20	100	60	4	20	9.5	1.26	54	-36	12	15	1100	T2
-0060	-0148	10												
-0061	-0149	20	220	60	8	32	15	0.91	29	-40	16	20	1400	T3
-0062	-0150	10												
-0063	-0151	20	270	60	9	36	13.5	0.67	23	-45	20	25	1850	T4
-0064	-0152	10												
-0065	-0153	20	22	75	3	12	4.25	2.57	157	-19	10	12	600	T1
-0066	-0154	10												

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V.
DCL is measured at rated voltage after 5 minutes.



MIL-PRF-39006 Series



Military Conventional Wet Tantalum

M39006/31 Dashes		Tolerance $\pm$ (%)	Cap (μ F) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	DC Leakage (μ A)		DF max (%)	ESR max (Ohms) at 120Hz	Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size
M Level	P Level				+25°C	+85°C & 125°C				-55°C	+85°C	+125°C		
-0067	-0155	20	82	75	4	24	7.6	1.23	63	-30	12	15	1000	T2
-0068	-0156	10												
-0069	-0157	20	180	75	9	36	12.2	0.9	30	-35	16	20	1300	T3
-0070	-0158	10												
-0071	-0159	20	220	75	10	40	18.5	1.12	24	-40	20	25	1800	T4
-0072	-0160	10												
-0073	-0161	20	10	100	3	12	2.25	2.99	200	-17	10	12	800	T1
-0074	-0162	10												
-0075	-0163	20	39	100	5	24	5.2	1.77	80	-20	12	15	1300	T2
-0076	-0164	10												
-0077	-0165	20	68	100	10	40	5.65	1.11	40	-30	14	16	1600	T3
-0078	-0166	10												
-0079	-0167	20	120	100	12	48	12.5	1.38	30	-35	15	17	2000	T4
-0080	-0168	10												

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V.
DCL is measured at rated voltage after 5 minutes.