CGA9N2X7R2A335M230KA

TDK Item Description : CGA9N2X7R2A335MT****

Lead Free | Halogen Free | REACH | RoHS COMPLIANT

Equivalent C5750X7R2A335M for Automotive


Characterization Sheet (Multilayer Ceramic Chip Capacitors)

Application & Main Feature

Automotive Grade (Mid Voltage (100 to 630V))

Series

CGA9(5750) [EIA CC2220]



Dimensions

L	5.70mm +/-0.4mm
W	5.00mm +/-0.4mm
T	2.30mm +/-0.2mm
B	0.20mm Min.
G	

Temperature Characteristic

X7R (-55 to 125 degC +/-15%)

Rated Voltage

2A (100Vdc)

Capacitance

3.3uF

Capacitance Tolerance

M (+/-20%)

Dissipation Factor

3% Max.


Insulation Resistance

151Mohm Min.


AEC-Q200

Yes


DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



TDK

All specifications are subject to change without notice.

January 4, 2016

Downloaded from Arrow.com.