



## Technical Data

11.07.2022

Heat shrinkable tubing 2:1 - flexible and coloured  
HFT-A - self extinguishing

HFT-A-19.0/9.5

Article Number 305-19004



Material:

Polyolefin, cross-linked (PO-X)

Colour:

Yellow (YE)

Supplied Ø D min.:

19.0 mm

Recov. Ø d max.:

9.5 mm

Wall (WT):

0.80 mm

Shrink Ratio:

2:1

Longitudinal Change After Shrinkage:

-5% max.

Min. Shrink Temperature - °C:

+135 °C

Flammability:

self-extinguishing, UL 224 VW-1

Operating Temperature - °C:

-55 °C to +135 °C

Heat Shock Test:

4h/200°C

Tensile Strength at Heat Shock:

13 MPa

Elongation at Heat Shock:

390 %

Behaviour At Low Temperature:

not cracking

IEC 60684-2

Dielectric Strength:

>21 kV/mm

IEC 60684-2

Insulation Class:

B (VDE 0530)

Tensile Strength:

14 MPa

IEC 60684-2

Elongation at break:

400%

IEC 60684-2

Specifications:

CLASS 903201, UL 224, VG 95343-5:2016-10

Test Method



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved