


CB61F

Fast-acting surface mount Brick™ fuses



Product features

- Fast-acting
- 2410 (6125 metric) compact footprint
- Designed to UL 248
- High interrupting ratings
- Current ratings from 2 A to 40 A
- Reflow and wave solder compatible
- Wire-in-air design
- Moisture sensitivity level (MSL): 1

Environmental compliance



Applications

Primary circuit protection


- Power supplies
- Servers
- Medical equipment
- White goods
- Battery chargers
- Consumer electronics
- Test equipment
- Battery pack protection

Agency information

- UL Listed cULus: File E19180, Guide JDYX (2 A - 15 A)
- UL Recognized cURus: File E19180, Guide JDYX2 (20 A - 40 A)
- CQC: CQC09012040316 (2 A - 6.3 A & 8 A - 10 A)

Ordering code

The ordering code is the part number replacing the " " with a "-" plus adding the packaging suffix.



Packaging suffix

- **-TR1** 1000 fuses on a 7" diameter tape and reel
- **-TR2** 5000 fuses on a 13" diameter tape and reel (2 A to 15 A only)



Powering Business Worldwide

Electrical characteristics

Amp Rating	% of Amp Rating	Opening Time
2 A – 40 A	100%	4 hours minimum
2 A – 15 A	200%	5 seconds maximum
20 A – 40 A	200%	60 seconds maximum


Product specifications

Part Number	Current rating (A)	Voltage rating (Vac)	Voltage rating (Vdc)	Interrupting rating ^{1,2} (A) @ rated voltage (Vdc)	Typical DC cold resistance ³ (mΩ)	Typical melting I ² t (A ² s)	Typical voltage drop ⁵ (mV)	Part marking	Agency approval cULus cURus CQC
CB61F2A	2.0	125	125	100 300	39	0.85	100	2	x x
CB61F3A	3.0	125	125	100 300	25	2.08	100	3	x x
CB61F4A	4.0	125	125	100 300	17	4.4	93	4	x x
CB61F5A	5.0	125	125	100 300	13	7.7	90	5	x x
CB61F6.3A	6.3	125	125	100 300	10	13.7	90	6.3	x x
CB61F7A	7.0	125	125	100 300	9	15.6	85	7	x
CB61F8A	8.0	125	125	100 300	8	19.5	90	8	x x
CB61F10A	10	125	125	100 300	6	36	90	10	x x
CB61F12A	12	125	125	50 200	5	40	90	12	x
CB61F15A	15	125	125	50 200	4	56	85	15	x
CB61F20A	20	-	72	- 500	2.3	210	60	20	x
CB61F25A	25	-	72	- 500	1.7	400	55	25	x
CB61F30A	30	-	72	- 500	1.2	900	50	30	x
CB61F40A	40	-	63	- 500	0.9	1600	50	40	x


1. AC Interrupting rating: Measured at rated voltage, 100% power factor
2. DC Interrupting rating: Measured at rated voltage, time constant of less than 50 microseconds, battery source
3. Typical DC cold resistance: Measured at 10% of rated current
4. Typical Pre-arcing I²t are measured at 10In Current
5. Typical voltage drop: Measured at rated current after temperature stabilizes

Dimensions—mm


2 A to 15 A




Recommended pad layout



20 A to 40 A




Recommended pad layout




Time current curve


2 A to 15 A



20 A to 40 A



Temperature derating curve



General specifications

Operating temperature: -55 °C to +125 °C (with derating)

Storage temperature: -55 °C to +125 °C

Thermal shock: 2 A to 15 A - MIL-STD-202, Method 107G, -65 °C/+125 °C, number of cycles :10
20 A to 40 A - MIL-STD-202, Method 107G -55 °C/+125 °C, number of cycles: 100


Bias humidity: 2 A to 15 A - MIL-STD-202, Method 103 +85 °C/85%RH. ,100 hours
20 A to 40 A - MIL-STD-202, Method 103 +85 °C/85%RH. ,1000 hours

Mechanical shock: 2 A to 40 A - MIL-STD-202G, Method 213B, Test condition C, 100 g's peak for 6 ms; Half-sine waveform

Mechanical vibration: 2 A to 15 A - MIL-STD-202G, Method 201, Test condition A (10 - 55 Hz, 0.06 inch, 2 hours each of 3 mutually perpendicular direction, total 6 hours), high Frequency: 20 g's for 20 min., 12 cycles each of 3orientations. ,10 - 2000 Hz.10 to 55 Hz, 0.06 inch, total excursion
20 A to 40 A - MIL-STD-202G, Method 201, 2 hours each of 3 orientations. Test from 10 -5 5 Hz in 1 minute

Resistance to solder heat: 2 A to 40 A - MIL-STD-202G, Method 210F , condition D (+260 °C, 10s)

Wave solder profile



Reference EN 61760-1:2006

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat		
• Temperature min. (T_{smin})	100 °C	100 °C
• Temperature typ. (T_{styp})	120 °C	120 °C
• Temperature max. (T_{smax})	130 °C	130 °C
• Time (T_{smin} to T_{smax}) (t_s)	70 seconds	70 seconds
Δ preheat to max Temperature	150 °C max.	150 °C max.
Peak temperature (T_p)*	235 °C – 260 °C	250 °C – 260 °C
Time at peak temperature (t_p)	10 seconds max 5 seconds max each wave	10 seconds max 5 seconds max each wave
Ramp-down rate	~ 2 K/s min ~3.5 K/s typ ~5 K/s max	~ 2 K/s min ~3.5 K/s typ ~5 K/s max
Time 25 °C to 25 °C	4 minutes	4 minutes

Manual solder

+350 °C (4-5 seconds by soldering iron), generally manual/hand soldering is not recommended

Solder reflow profile




Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm)	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60-120 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	30 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2024 Eaton
All Rights Reserved
Printed in USA
Publication No. 4377 PCN24012
April 2024

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

