Specifications

Eaton GSGB30

Fuse-link, high speed, 30 A, AC 660 V, DC 400 V, BS88, 17 x 80 mm, aR, BS, Ultra fast

General specifications

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	GSGB30
UPC	051712392273
EAN	5027590502719
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	18 mm
PRODUCT WIDTH	18 mm
PRODUCT WEIGHT	33.25 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Recognized
GLOBAL CATALOG	GSGB30

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

AMPERAGE RATING	30 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	100 kA
RATED VOLTAGE AC	660 V
RATED VOLTAGE DC	400 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	61.8 mm
MOUNTING DIMENSION	M6
CURRENT TYPE	AC/DC
CLASS	Class aR
WATT LOSSES	9.6 W
FUSE SHAPE	Offset bolted tags
COLOR	None
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	GSG
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

Resources

BROCHURES	eaton-bussmann-series-bs88-high-speed-fuses-product-aid-pa135003en-us.pdf
CATALOGS	eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf GSGB30~Eaton Bussmann series high speed British standard fuse Bussmann series complete full line catalog no. 1007
MCAD MODEL	eaton-hs-bs88-body-fuses-mcad-3d-models-gsgb-16-63a.stp

Downloaded from Arrow.com.

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.