SiC Power Module

BSM180D12P2E002

Datasheet

●Application


· Motor drive

· Inverter, Converter

· Photovoltaics, wind power generation.

· Induction heating equipment.

●Circuit diagram



●Features

1) Low surge, low switching loss.


2) High-speed switching possible.

3) Reduced temperature dependence.

●Construction

This product is a half bridge module consisting of SiC-DMOSFET and SiC-SBD from ROHM.

●Dimensions & Pin layout (Unit : mm)



© 2016 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●**Absolute maximum ratings** (T_j = 25°C)


Parameter	Symbol	Conditions	Limit	Unit
Drain-source voltage	V_{DSS}	G-S short	1200	V
Gate-source voltage(+)	V_{GSS}	D-S short	22	
Gate-source voltage(–)			–6	
G - S Voltage (t_{surge}<300nsec)	V_{GSS_surge}	D-S short	–10 to 26	
Drain current *1	I_D	DC (T_c=60°C)	204	A
	I_{DRM}	Pulse (T_c=60°C) 1ms *2	360	
	I_{DRM}	Pulse (T_c=60°C) 10us *2	540	
Source current *1	I_S	DC (T_c=60°C) V_{GS}=18V	204	
	I_{SRM}	Pulse (Tc=60°C) 1ms V_{GS}=18V *2	360	
	I_{SRM}	Pulse (Tc=60°C) 10us V_{GS}=18V *2	540	
Total power disspation *3	Ptot	T_c=25°C	1360	W
Max Junction Temperature	T_{jmax}		175	°C
Operating junction temperature	T_{jop}		–40 to150	
Storage temperature	T_{stg}		–40 to125	
Isolation voltage	Visol	Terminals to baseplate, f=60Hz AC 1min.	2500	Vrms
Mounting torque	–	Main Terminals : M6 screw	4.5	N · m
		Mounting to heat shink : M5 screw	3.5	

(*1) Case temperature (T_c) is defined on the surface of base plate just under the chips.

(*2) Repetition rate should be kept within the range where temperature rise if die should not exceed $T_{j\,max.}$

(*3) T_j is less than 175°C

Example of acceptable V_{GS} waveform



© 2016 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●Electrical characteristics (T_j=25°C)


Parameter	Symbol	Conditions		Min.	Typ.	Max.	Unit
Static drain-source on-state voltage	$V_{DS(on)}$	I_D180A, V_{GS}=18V	T_j=25°C	-	2.2	3.2	V
			T_j=125°C	-	3.1	-	
			T_j=150°C	-	3.5	5.0	
Drain cutoff current	I_{DSS}	V_{DS}=1200V, V_{GS}=0V		-	-	3.2	mA
Source-drain voltage	V_{SD}	V_{GS}=0V, I_S=180A	T_j=25°C	-	1.6	2.2	V
			T_j=125°C		2	-	
			T_j=150°C	-	2.2	3.3	
		V_{GS}=18V, I_S=180A	T_j=25°C	-	1.3	-	
			T_j=125°C		1.5	-	
			T_j=150°C	-	1.6	-	
Gate-source threshold voltage	$V_{GS(th)}$	V_{DS}=10V, I_D=35.2mA		1.6	-	4	V
Gate-source leakage current	I_{GSS}	V_{GS}=22V, V_{DS}=0V		-	-	0.5	μA
		V_{GS}= −6V, V_{DS}=0V		−0.5	-	-	
Switching characteristics	$t_{d(on)}$	$V_{GS(on)}$=18V, $V_{GS(off)}$=0V		-	45	-	ns
	t_r	V_{DS}=600V		-	45	-	
	t_{rr}	I_D=180A		-	45	-	
	$t_{d(off)}$	$R_{G(on)}$=1.0Ω, R_G=0.2Ω		-	125	-	
	t_f	inductive load		-	45	-	
Input capacitance	Ciss	V_{DS}=10V, V_{GS}=0V, 200kHz		-	18	-	nF
Gate Registance	R_{Gint}	T_j=25°C		-	1.2	-	Ω
NTC Rated Resistance	R25				5.0		kΩ
NTC B Value	B50/25				3370		K
Stray Inductance	Ls				13.0	-	nH
Creepage Distance	-	Terminal to heat sink			14.5	-	mm
		Terminal to terminal			15.0	-	mm
Clearance Distance	-	Terminal to heat sink			12.0	-	mm
		Terminal to terminal			9.0	-	mm
Junction-to-case thermal resistance	R_{th}(j-c)	DMOS (1/2 module) *4		-	-	0.11	°C/W
		SBD (1/2 module) *4		-	-	0.14	
Case-to-heat sink Thermal resistance	R_{th}(c-f)	Case to heat sink, per 1 module, Thermal grease applied *5		-	0.035	-	

(*4) Measurement of Tc is to be done at the point just under the chip.

(*5) Typical value is measured by using thermally conductive grease of λ=0.9W/(m・K).

(*6) If the Product is used beyond absolute maximum ratings defined in the Specifications, as its internal structure may be dameged, please replace such Product with a new one.

＜Wavelength for Switching Test＞



© 2016 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●Electrical characteristic curves (Typical)

Fig.1 Typical Output Characteristics [T_j=25ºC]




Fig.2 Drain-Source Voltage vs. Drain Current




Fig.3 Drain-Source Voltage vs. Gate-Source Voltage [T_j=25ºC]





Fig.4 Static Drain - Source On-State Resistance vs. Junction Temperature



© 2016 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●**Electrical characteristic curves** (Typical)

Fig.5 Forward characteristic of Diode




Fig.6 Forward characteristic of Diode




Fig.7 Drain Current vs. Gate-Source Voltage





Fig.8 Drain Current vs. Gate-Source Voltage



© 2016 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●Electrical characteristic curves (Typical)

Fig.9 Switching Characteristics [T_j=25ºC]




Fig.10 Switching Characteristics [T_j=125ºC]




Fig.11 Switching Characteristics [T_j=150ºC]





Fig.12 Switching Loss vs. Drain Current [T_j=25ºC]



© 2016 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●Electrical characteristic curves (Typical)

Fig.13 Switching Loss vs. Drain Current [T_j=125ºC]




Fig.14 Switching Loss vs. Drain Current [T_j=150ºC]




Fig.15 Recovery Characteristics vs. Drain Current [T_j=25ºC]





Fig.16 Recovery Characteristics vs. Drain Current [T_j=125ºC]



© 2016 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●Electrical characteristic curves (Typical)

Fig.17 Recovery Characteristics vs. Drain Current [T_j=150ºC]




Fig.18 Switching Characteristics vs. Gate Resistance [T_j=25ºC]




Fig.19 Switching Characteristics vs. Gate Resistance [T_j=125ºC]





Fig.20 Switching Characteristics vs. Gate Resistance [T_j=150ºC]



© 2016 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●Electrical characteristic curves (Typical)

Fig.21 Switching Loss vs. Gate Resistance
[T_j=25ºC]




Fig.22 Switching Loss vs. Gate Resistance
[T_j=125ºC]




Fig.23 Switching Loss vs. Gate Resistance
[T_j=150ºC]





Fig.24 Typical Capacitance vs. Drain-Source Voltage



© 2016 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●Electrical characteristic curves (Typical)

Fig.25 Gate Charge Characteristics
[T_j=25ºC]





Fig.26 Normalized Transient Thermal Impedance



© 2016 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

Notes

1) The information contained herein is subject to change without notice.

2) Before you use our Products, please contact our sales representative and verify the latest specifications.

3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.
Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.

4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.

6) The Products specified in this document are not designed to be radiation tolerant.

7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, and power transmission systems.

8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.

9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.

10) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.

11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.

12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.

13) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.

ROHM SEMICONDUCTOR

Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/

© 2012 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.