
Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten

INDUSTRIAL@AMPHENOL
TRUSTED GLOBALLY















Assembly instruction see N 22 091 0025

Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	14	19
Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	14-b	19-a
Rated voltage	IEC 60664-1	150 V		100 V	32 V	100 V		32 V					
Rated impulse withstand voltage	IEC 60664-1	1500 V			800 V	1500 V		800 V					
Pollution degree	IEC 60664-1	3[1]											
Installation category	IEC 60664-1	I											
Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600											
Current rating	IEC 60512-5-2 UL 1977	10A/+40°C		7A/+40°C						3A/+40°C			
Insulation resistance	IEC 60512-3-1	>10^{10} Ohm[2]											
Contact resistance	IEC 60512-2-1	<5mOhm											
Climatic category	IEC 60668-1	40 / 100 / 21											
Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F											
Salt spray resistance	DIN IEC 60068-2-11, test Ka	720h											
IP degree	ÎEC 60529	IP69K / IP 68 (in mated condition)											
Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	50N	60N
mechanical operation	IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles											
housing material		brass and / or zinc die cast, nickel plated											
dielectric material		thermoplastic											
sealing material		Chloroprene											
contacts		silver or gold plated											
termination technique		solder											
wire gauge		≤0,5mm² / 20 AWG								≤0,35mm² / 22 AWG			
flamability		UL 94 V0											
locking system	DIN EN 61076-2-106	metal screw coupling; tightening torque 0,7 - 1,5 Nm											

[1] designed according pollution degree 2, can be used under pollution degree 3 if the rules according IEC 60664-1 are fulfiled
[2] under operating conditions >10^{8} Ohm

Do not connect or disconnect under load. Metal housing parts shall be securely incoporated to protected ground.
Remark for gold plated contacts:
In order to avoid brittle inter-metallic connections, gold plated terminals have to be tin-plated in the solder area.
All technical data have been measured in a laboratory environment and can be different during pratical usage of the product. Any product information is for descriptive usage only and not legally binding; particulary the information does not constitute or provide any legal guaranties ("Beschaffenheitsgarantie" or " Haltbarkeitsgarantie").

Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. IEC 61076-2-106)	Part number with silver plated contacts	Part number with gold plated contacts
	19 (19-a)	C091 31D019 102 4 U	C091 31D019 202 4 U
	14 (14-b)	C091 31D114 102 4 U	C091 31D114 202 4 U
	14 (14-a)	C091 31D014 102 4 U	C091 31D014 202 4 U
	12 (12-a)	C091 31D012 102 4 U	C091 31D012 202 4 U
	8 (08-a)	C091 31D008 102 4 U	C091 31D008 202 4 U
	7 (07-b)	C091 31D107 102 4 U	C091 31D107 202 4 U
	7 (07-a)	C091 31D007 102 4 U	C091 31D007 202 4 U
	6 (06-a)	C091 31D006 102 4 U	C091 31D006 202 4 U
	5 (05-b)	C091 31D105 102 4 U	C091 31D105 202 4 U
	5 (05-a)	C091 31D005 102 4 U	C091 31D005 202 4 U
	4 (04-a)	C091 31D004 102 4 U	C091 31D004 202 4 U
	3 (03-a)	C091 31D003 102 4 U	C091 31D003 202 4 U

Gewicht (errechnet) / *Calc WT*: 0,051 kg
Prüfmaß / *Testdimension*
Teileindex / *Partindexnumber:*
Bagatelle change:

Zul. Abw./ *Tolerances*: ISO 2768-c
DIN / ISO 13715

Maßstab / *Scale*: 2:1 2:1 | A3

CUSTOMER DRAWING

Index	Änderung/ *Description*	Datum/ *Date*	Name
03	202000083	26.10.2020	MCARL

Gez. 26.05.2020
Drawn MCARLE
Status Released
Gepr. 11.01.2021
Checked MBERTSCH

Amphenol Tuchel Industrial GmbH

Female cable connector
for cable diameter 8-10,5 mm

M C091 31DXXX X02 4 U

Blatt/ *Sheet* 1 | 1 Bl.

Ers. f. / *Replacement for*: M-C091 31DXXX X02 4 U Rev02

NXM-V02 | FAI2020-001724

Downloaded from Arrow.com.