Pushing Performance
Since 1945

Han Domino Pneumatic cube (MF.1)




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 931 1001
Specification	Han Domino Pneumatic cube (MF.1)
HARTING eCatalogue	https://harting.com/09149311001

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Domino Pneumatic Cube
Size of the module	Domino module
Description of the module	Small tab

Version

Gender	Male Female
Number of contacts	1
Details	Please order contacts separately.

Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥10,000

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	Blue
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984 IEC 61373 Category 2
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	2
Net weight	4.1 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140185296
eCl@ss	27440220 Module for industrial connectors (pneumatic)
ETIM	EC000438
UNSPSC 24.0	39121552

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.