



Part Number : [640016200](#)

Product Description : Hand Crimp Tool

Series Number : 207129

Status : Active

Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

[ATS-640016200-001.pdf](#)

[TM-640160065-001.pdf](#)

[TM-640160065CN-001.pdf](#)

[TM-640160065SP-001.pdf](#)

[TM-640160065IT-001.pdf](#)

[TM-640160065JP-001.pdf](#)

[TM-640160065KR-001.pdf](#)

[TM-640160065MY-001.pdf](#)

[TM-640160065PL-001.pdf](#)

[TM-640160065RU-001.pdf](#)

[TM-640160065SK-001.pdf](#)

[TM-640160065TH-001.pdf](#)

[TM-640160065VN-001.pdf](#)

[TM-640160065TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per per ED/30/2017 (7 July 2017)

EU RoHS	Not Reviewed per EU 2015/863
---------	------------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool
Comments	Field Repair, See Tooling Specification (PDF) Above. Type RHT
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	822350860390
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and

	sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
--	--

Applicable Parts

Description	Part Number
InsulKrimp Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 12-10 AWG, Yellow Insulator, Bag	<u>190110039</u>
InsulKrimp Fully Insulated Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 12-10 AWG, Yellow Insulator, Loose in a Bag	<u>190130033</u>
InsulKrimp Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 22-18 AWG, Red Insulator, Loose	<u>190110035</u>
InsulKrimp Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 16-14 AWG, Blue Insulator, Loose	<u>190110037</u>

This document was generated on Sep 11, 2025